

## Fiber Optic Taper For 25mm to 8mm



Stock #55-138 **2 In Stock**

MRP ₹1,83,267

**i** Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1+	₹1,83,267 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

#### General

50 / 50 **Core/ Clad Ratio:**

#### Physical & Mechanical Properties

±0.5, Large End **Diameter Tolerance (mm):**

25.00 **Height (mm):**

27.00 **Diameter of Large End (mm):**

25:8 mm	<b>Size Ratio:</b>
8.70	<b>Size of Small End (mm):</b>
±0.1	<b>Thickness Tolerance (mm):</b>
±0.1	<b>Dimensional Tolerance (mm):</b>

## Optical Properties

3.00	<b>Distortion (%):</b>
<a href="#">Schott 24 Glass with EMA</a>	<b>Substrate:</b> <input type="checkbox"/>
1.00	<b>Numerical Aperture NA:</b>
72 lp/mm	<b>Resolution:</b>
30-20	<b>Surface Quality:</b>
8.00	<b>Resolving Power (µm):</b>

## Material Properties

6.8	<b>Coefficient of Thermal Expansion CTE (10<sup>-6</sup>/°C):</b>
-----	---

## Environmental & Durability Factors

-10 to +300	<b>Operating Temperature (°C):</b>
-------------	------------------------------------

## Regulatory Compliance

<a href="#">View</a>	<b>Certificate of Conformance:</b>
United States	<b>Country of Origin:</b>
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	<b>Imported By:</b>

## Product Details

- Coherent Arrangement of Fibers
- Made with EMA Fibers to Absorb Light
- Round-to-Round or Round-to-Rectangular Tapers Types Available

Fiber Optic Tapers utilize a coherent fiber optic plate that transmits either a magnified or reduced image from its input surface to its output surface. These low distortion tapers are made with EMA Fibers to absorb light and are optimized for 1/2" or 2/3" sensor chip sizes. Magnification is a ratio of the diameters of the large and small ends of the tapers. Typical applications include image magnification or reduction, sensor coupling, fluoroscopy, and light sensors.

Fiber Optic Faceplates transmit images from input surface to output surface using coherent fibers. Common uses include CRT/LCD displays, sensor coupling, X-ray imaging and image intensification. All tapers and faceplates are suitable for visible and NIR applications and feature beveled edges.