

# Flat Dome Light LFXV-50SW

See More by [CCS](#)



Stock #19-962 **1 In Stock**

- 1 + MRP ₹2,16,117

Price inclusive of all taxes

**ADD TO CART**

### Volume Pricing

Qty 1+	₹2,16,117 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

Model Number:  
LFXV-50SW

Type of Illumination:  
LED Illuminator

Manufacturer:  
CCS

Geometry:  
Flat Dome Light

Illumination Mode:

Constant

## Physical & Mechanical Properties

93 x 93 x 10 **Dimensions (mm):**

190 **Weight (g):**

50 x 50 **Active Area (mm):**

## Optical Properties

White **Color:**

## Electrical

9.9 **Power Consumption (W):**

## Hardware & Interface Connectivity

24 **Input Voltage (V):**

**Power Supply:**  
Power Supply Required and Sold Separately.  
USA: [#73-491](#)  
Europe: [#73-491](#)  
Japan: [#89-513](#)  
Korea: [#33-773](#)  
China: [#73-491](#)

## Environmental & Durability Factors

5,500 **Color Temperature (K):**

## Regulatory Compliance

[View](#) **Certificate of Conformance:**

Japan **Country of Origin:**

**Imported By:**  
Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Product Details

- Thin, Compact, and Lightweight Housing
- Available in Multiple LED Colors
- Wide Range of Sizes Including Square and Rectangular Shapes

CCS Flat Dome Lights are ideal for achieving illumination similar to Coaxial or Dome Lights in a lighter, more compact unit. While standard dome lights are good for creating a diffuse lighting environment that minimizes specular reflection, their mechanical size and imaging aperture through a small hole on top limit their use in compact applications. These flat dome lights provide the same diffuse illumination environments as a standard dome light but in a 10mm thick, flat housing with a large imaging area, greatly increasing the options for working distance, depth of focus, and field of view. CCS Flat Dome Lights can also be used at long working distances to recreate the illumination environment of a coaxial light, which is used to reduce shadowing and has minimal glare. This flexibility makes these flat dome lights suitable for a wide range of industrial and imaging applications, particularly when imaging textured, shiny, or uneven surfaces.


## Technical Information

### Imaging Examples

Introducing various examples using unique characteristics of the Flat Dome Lights


#### Electronic Components Industry

Imaging Characters on a Textured Metal Surface



#### Electronic Components Industry

Imaging Characters on Button Batteries




## Packaging Industry

### Imaging Shrink Film of Containers



Conventional product

Ring Light (Blue)



The shrink film is poorly imaged.

New product

LFX3-100BL (Blue)



The shrink film is clearly imaged.