

[See all 12 Products in Family](#)

TECHSPEC[®] Gardasoft TR-CL180 Industrial Lens Controller



Gardasoft TR-CL180 Industrial Lens Controller



Stock **#13-803** 2 In Stock

-

1

+

₹1,17,000

ADD TO CART

Volume Pricing	
Qty 1+	₹1,17,000 each
Need More?	Request Quote

Product Downloads

General	
Lens Accessory	Type:
TR-CL180	Model Number:
Physical & Mechanical Properties	
120 x 101 x 35	Dimensions (mm):

175	Weight (g):
Electrical	
-400 to +400	Operating Current (mA):
Hardware & Interface Connectivity	
6-way Hirose	Connector:
Environmental & Durability Factors	
5 to 50	Operating Temperature (°C):
Regulatory Compliance	
View	Certificate of Conformance:
United Kingdom	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- Liquid Lens for Extended Depth of Field Telecentric Lens
- Up to 2.3 MegaPixels, 4.5µm Pixel Size Sensors
- Up to 2/3", C-Mount Telecentric Lens
- Magnification from 0.15X to 0.75X

TECHSPEC® MercuryTL™ Liquid Lens Telecentric Lenses combine the capabilities of a telecentric lens with the flexibility of a liquid lens. These lenses combine the unique feature of telecentric lenses, eliminating parallax (or perspective) error, with a liquid lens, allowing for the focus to be electronically controlled. This combination provides quick working distance adjustment, while maintaining telecentricity, distortion, and image performance throughout the entire working distance range. TECHSPEC® MercuryTL™ Liquid Lens Telecentric Lenses are ideal for gauging, measurement, and placement applications where quick depth of field adjustment is required.

As the liquid lens is used to focus the telecentric lens, its curvature changes. As its curvature changes, there will be small changes in the ray angles in the rear of the lens (incident on the image sensor). As a result, there are small field of view changes over the working distance range as the liquid lens refocuses the lens. However, the front (object space) ray angles are unaffected by the liquid lens changing curvature, allowing the telecentric lens to maintain telecentricity over the entire working distance range.

Note: Hirose cables and [Liquid Lens Driver](#) sold separately.

Technical Information

