

[See all 10 Products in Family](#)

Handheld IR Viewer, 350-2000nm, 1X Magnification



Stock **#72-753** [CONTACT US](#)

-

1

+

₹2,51,100

ADD TO CART

Volume Pricing	
Qty 1+	₹2,51,100 each
Need More?	Request Quote

Product Downloads

General	
50	Operating Lifetime (hours):
40	Field of View (°):
Note: Includes C-mount adapter. The thread of the viewer itself is M28X0,75mm, lens is C-mount.	
Physical & Mechanical Properties	
153 x 184 x 51	Dimensions (inches):

400	Weight (g):
Optical Properties	
1X	Magnification:
60 Lp/mm	Resolution:
350 - 2000	Spectral Response (nm):
0.1 to ∞	Focus Range (mm):
Environmental & Durability Factors	
-10 to +40	Operating Temperature (°C):
Regulatory Compliance	
View	Certificate of Conformance:
Lithuania	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- Indirectly View IR Light Sources and Lasers
- Bright, High Contrast Images
- Suitable for CW or Ultrafast Laser Inspection

Handheld Infrared (IR) Viewers are available in three sensitivity ranges for infrared detection up to 1300nm, 1700nm, or 2000nm. Otherwise invisible IR wavelengths are viewable as a green fluorescent image through the included eyepiece by employing a proprietary high resolution image converter and photocathode arrangement to produce a visible image from infrared radiation. Each IR Viewer includes a C-mount objective lens for macro viewing (except #72-754 and #72-755, which are M28 x 0.75mm threaded) and Edmund Optics offers a wide range of available C-mount lenses for alternate working distance or fields of view requirements. A 1/4-20 mount in the base of the handle allows for easy positional adjustment and easy integration with benchtop or tripod mounted systems. Handheld Infrared (IR) Viewers allow viewing of CW laser radiation as well as ultrafast pulsed laser radiation with pulse durations from ps to μs without synchronization. These IR Viewers are ideal for applications such as IR laser alignment, semiconductor wafer inspection, identifying faults in fiber systems, aligning laser cavities, inspecting food and fluids, and IR light visualization in biological, medical, and electronic applications.

Note: These products are not intended for direct beam viewing or viewing “mid air” beams as over exposure can damage the optics. For best results with an IR laser source, view a diffuse source, such as a detection card in the beam path.