


# Harsh Environment Transmission Dip Probe Tip, 50 mm

See More by [Ocean Optics](#)



Stock #90-583 NEW **1 In Stock**

- 1 + MRP ₹64,463

Price inclusive of all taxes

**ADD TO CART**

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | ₹64,463 each                  |
| Need More?     | <a href="#">Request Quote</a> |

## Product Downloads

Titanium **Construction Material:**

## General

RT-TI-50MM **Model Number:**

## Optical Properties

200 - 2500 **Wavelength Range (nm):**

## Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **Reach 250:**

United States **Country of Origin:**

Edmund Optics India Private Limited **Imported By:**

## Product Details

- Transmission Dip Probes Designed for Reliable In-Solution Absorbance/Transmission Measurements
- Rugged Stainless Steel or PEEK for Tough Process Conditions and Harsh Environments
- Flexible Path Lengths Available with Interchangeable Probe Tips
- Compatible with Ocean Optics Spectrometers and Accessories

Ocean Optics Transmission Dip Probes couple to spectrometers and light sources to measure absorbance and transmission in solutions. Choose from ruggedized high-pressure probe ([#90-569](#)) for demanding process environments or PEEK-jacketed probes ([#90-570](#) and [#90-571](#)) for harsh chemical conditions, spanning UV–VIS to VIS–NIR wavelengths. Easily customize your setup with accessories such as interchangeable probe tips in various path lengths and the protective sleeve ([#90-585](#)) for extended durability in corrosive or high-temperature applications. Ocean Optics Transmission Dip Probes are designed for seamless integration with [Ocean Optics spectroscopy systems and compatible accessories](#).

## Technical Information

| Transmission Dip Probe                   | Transmission Dip Probe Stock Number | Compatible Transmission Dip Probe Tip                       | Compatible Transmission Dip Probe Tip Stock Number |
|--|-------------------------------------|---|--|
| UV-VIS Heavy-Duty Transmission Dip Probe | <a href="#">#90-569</a>             | Harsh Environment Transmission Dip Probe Tip, 2 mm          | <a href="#">#90-582</a>                            |
|  |                                     | Harsh Environment Transmission Dip Probe Tip, 5 mm          | <a href="#">#90-584</a>                            |
|  |                                     | Harsh Environment Transmission Dip Probe Tip, 10 mm         | <a href="#">#90-580</a>                            |
|  |                                     | Harsh Environment Transmission Dip Probe Tip, 25 mm         | <a href="#">#90-581</a>                            |
|  |                                     | Harsh Environment Transmission Dip Probe Tip, 50 mm         | <a href="#">#90-583</a>                            |
| UV-VIS Transmission Dip Probe            | <a href="#">#90-570</a>             | Stainless Steel Transmission Dip Probe Tip, 2 mm            | <a href="#">#90-573</a>                            |
|  |                                     | Stainless Steel Transmission Dip Probe Tip, 5 mm            | <a href="#">#90-576</a>                            |
|  |                                     | Stainless Steel Transmission Dip Probe Tip, 10 mm           | <a href="#">#90-572</a>                            |
|  |                                     | Adjustable Path Length Transmission Dip Probe Tip, 2–10 mm  | <a href="#">#90-578</a>                            |
|  |                                     | Adjustable Path Length Transmission Dip Probe Tip, 10–20 mm | <a href="#">#90-577</a>                            |
| VIS-NIR Transmission Dip Probe           | <a href="#">#90-571</a>             | Stainless Steel Transmission Dip Probe Tip, 2 mm            | <a href="#">#90-573</a>                            |
|  |                                     | Stainless Steel Transmission Dip Probe Tip, 5 mm            | <a href="#">#90-576</a>                            |
|  |                                     | Stainless Steel Transmission Dip Probe Tip, 10 mm           | <a href="#">#90-572</a>                            |
|  |                                     | Adjustable Path Length Transmission Dip Probe Tip, 2–10 mm  | <a href="#">#90-578</a>                            |
|  |                                     | Adjustable Path Length Transmission Dip Probe Tip, 10–20 mm | <a href="#">#90-577</a>                            |