

[See all 59 Products in Family](#)

Helios2 + Triton Mount

See More by [LUCID Vision Labs™](#)



Helios2 + Triton Mount



Stock #25-149 **2 In Stock**

- 1 + ₹4,200

ADD TO CART

Volume Pricing

Qty 1+	₹4,200 each
Need More?	Request Quote

Product Downloads

General

Camera Accessory **Type:**

HLT-TRI-MNT **Model Number:**

Note:
Triton to Helios2 mounting bracket with 8 screws (4x M4 and 4x M3 with washers)

Regulatory Compliance

Certificate of Conformance:

[View](#)

Country of Origin:

Malaysia

Imported By:

Edmund Optics India Private Limited

Product Details

- Compact 29 x 29 x 45mm Form Factor
- Global, Rolling, or Polarized CMOS Sensors
- IP67 Protection with Optional Lens Tubes

LUCID Vision Labs Triton™ GigE Power over Ethernet (PoE) Cameras provide exceptional price performance in a compact 29 x 29mm form factor. These cameras are available with Sony's Pregius™ and Starvis™ imaging sensors with up to 24.5 megapixels of resolution, as well as Sony's polarized sensor. Each imaging sensor is actively aligned during manufacturing, ensuring sharp and crisp images even in the corners. Using the accessory IP67 lens tubes (sold separately), LUCID Vision Labs Triton GigE Power over Ethernet (PoE) Cameras can operate in harsh environments where dust or water are present up to IP67 thresholds. Triton cameras are ideal for automotive, process control, and food and beverage applications.