

[See all 6 Products in Family](#)

**TECHSPEC®**

**Max PeakPower Low-GDD Ultrafast Dielectric Mirror, 920nm, 45° AOI, 12.7mm Dia., 6.35mm Thick**



Stock #29-523 **20+ In Stock**

MRP ₹36,926

● Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-5	₹36,926 each
Qty 6+	₹35,211 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**Physical & Mechanical Properties**

12.70 +0.00/-0.10      **Diameter (mm):**

6.35 ±0.10      **Thickness (mm):**

Commercial Polish      **Edges:**

Bevel:

Protective as needed

## Optical Properties

**Surface Quality:**

10-5

**Coating Specification:**

$R_s > 99.50\%$  @ 830 - 1010nm @ 45° AOI

$R_p > 99.50\%$  @ 840 - 997nm @ 45° AOI

**GDD Specification:**

$0 \pm 50 \text{ fs}^2$  @ 830 - 1010nm @ 45° AOI (s-pol)

$0 \pm 50 \text{ fs}^2$  @ 861 - 966nm @ 45° AOI (p-pol)

**Surface Flatness (P-V):**

$\lambda/10$

**Design Wavelength DWL (nm):**

830 - 1010

**Damage Threshold, Reference:**

$0.75 \text{ J/cm}^2$  @ 920nm, 100-on-1, S-Polarization, 5Hz,  
Pulse Duration 25fs, 350 $\mu\text{m}$  Dia.

## Regulatory Compliance

**Certificate of Conformance:**

[View](#)

**Country of Origin:**

Japan

**Imported By:**

Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Product Details

- High Femtosecond Laser Damage Threshold exceeding  $0.75 \text{ J/cm}^2$  for 25fs Pulse Duration at 920nm
- $> 99.5\%$  Reflectivity with Near Zero Group Delay Dispersion
- [Platinum-Level 2024 Laser Focus World \(LFW\) Innovators Award](#)

TECHSPEC® PeakPower High LDT Low GDD Ultrafast Mirrors utilize an innovative design approach to maximize laser damage threshold for ultrafast pulses. These mirrors boast a near  $0 \text{ fs}^2$  GDD over a broad spectral bandwidth, making them suitable for the most demanding ultrafast applications. A  $45^\circ$  angle of incidence makes them perfectly suitable as turn mirrors in advanced ultrafast laser systems. TECHSPEC® PeakPower High LDT Low GDD Ultrafast Mirrors' high reflectivity ensures minimal loss while maintaining ultrashort pulse durations. The outstanding high laser damage threshold (LDT) values exceeding  $0.75 \text{ J/cm}^2$  for 25fs Pulse Duration at 920nm for these mirrors ensures they will perform even under exceptionally high ultrafast pulse energies.

## Coating Curves