

[See all 6 Products in Family](#)

TECHSPEC®

Max PeakPower Low-GDD Ultrafast Dielectric Mirror, 920nm, 45° AOI, 50.8mm Dia., 9.53mm Thick



Stock #29-525 **10 In Stock**

- 1 + MRP ₹85,253

Price inclusive of all taxes

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1-5 | ₹85,253 each |
| Qty 6-25 | ₹81,217 each |
| Need More? | Request Quote |

Product Downloads

Physical & Mechanical Properties

50.80 +0.00/-0.10 **Diameter (mm):**

9.53 ±0.10 **Thickness (mm):**

Commercial Polish **Edges:**

Bevel:

Protective as needed

Optical Properties

Surface Quality:

10-5

Coating Specification:

$R_s > 99.50\%$ @ 830 - 1010nm @ 45° AOI
 $R_p > 99.50\%$ @ 840 - 997nm @ 45° AOI

GDD Specification:

$0 \pm 50 \text{ fs}^2$ @ 830 - 1010nm @ 45° AOI (s-pol)
 $0 \pm 50 \text{ fs}^2$ @ 861 - 966nm @ 45° AOI (p-pol)

Surface Flatness (P-V):

$\lambda/10$

Design Wavelength DWL (nm):

830 - 1010

Damage Threshold, Reference:

0.75 J/cm^2 @ 920nm, 100-on-1, S-Polarization, 5Hz,
Pulse Duration 25fs, 350 μm Dia.

Regulatory Compliance

Certificate of Conformance:

[View](#)

Country of Origin:

Japan

Imported By:

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- High Femtosecond Laser Damage Threshold exceeding 0.75 J/cm^2 for 25fs Pulse Duration at 920nm
- $> 99.5\%$ Reflectivity with Near Zero Group Delay Dispersion
- [Platinum-Level 2024 Laser Focus World \(LFW\) Innovators Award](#)

TECHSPEC® PeakPower High LDT Low GDD Ultrafast Mirrors utilize an innovative design approach to maximize laser damage threshold for ultrafast pulses. These mirrors boast a near 0 fs^2 GDD over a broad spectral bandwidth, making them suitable for the most demanding ultrafast applications. A 45° angle of incidence makes them perfectly suitable as turn mirrors in advanced ultrafast laser systems. TECHSPEC® PeakPower High LDT Low GDD Ultrafast Mirrors' high reflectivity ensures minimal loss while maintaining ultrashort pulse durations. The outstanding high laser damage threshold (LDT) values exceeding 0.75 J/cm^2 for 25fs Pulse Duration at 920nm for these mirrors ensures they will perform even under exceptionally high ultrafast pulse energies.

Coating Curves