

# Infinite Mounting Clamp

See More by [Infinity Photo-Optical Company](#)



Stock #54-591 CLEARANCE **1 In Stock**

⊖ 1 ⊕ MRP ₹5,411

● Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1+	₹5,411 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Lens Accessory **Type:**

**Regulatory Compliance**

**Compliant** RoHS 2015:

**Compliant** Reach 224:

Certificate of Conformance:

## Country of Origin:

United States

## Imported By:

Edmund Optics India Private Limited  
 267, Greystone Building, Second Floor,  
 6th Cross Rd, Binnamangala,  
 Stage 1, Indiranagar, Bengaluru,  
 Karnataka, India 560038  
 Phone: +91- 80-6845 0000


## Product Details

- 3 Primary Magnification Range Options
- Working Distance from 25mm to Infinity
- Optional **LDL** Doubler Tube Boosts Magnification 2X

The InfiniMte™ Imaging Lenses are available in 3 lens power ranges. The standard version uses an integral focus lock as a friction brake to lock the magnification/focus setting in place. Designed with input from specialists in the field, its miniature size allows the InfiniMte™ to be integrated into a wide variety of electronic imaging conditions. The length of the lens does not change when focusing. InfiniMte™ Imaging Lenses were designed to provide specific working distance and field of view combinations when using 1/3" format sensors, but the lenses can be used with sensors up to 2/3" format.

The main lens, the Alpha, covers a 0.75- 0.08X range for macro use, whereas the Beta and Gamma versions offer a working distance (WD) shift from the high-magnification end of the Alpha. For example, with a 1/2" sensor, the Alpha gives a 1/2" field of view (FOV) at 40mm WD at 0.5X Lens magnification (PM); at the same PM & FOV, the Beta has a 60mm WD and the Gamma has a 122mm WD. The three lens options offer unprecedented flexibility in system integration.

## Technical Information



Units: mm

Working Distance	25mm	40mm	60mm	80mm	170mm	230mm	295mm
Primary Magnification	0.75X	0.50X	0.33X	0.25X	0.13X	0.10X	0.08X
Field of View, 1/2" Sensor Horiz	8.5mm	12.8mm	19.4mm	25.6mm	51.2mm	64.0mm	80.0mm
Field of View, 1/3" Sensor Horiz	6.4mm	9.6mm	14.5mm	19.2mm	38.4mm	48.0mm	60.0mm

Working Distance	55mm	60mm	90mm	120mm	240mm	317mm	400mm
Primary Magnification	0.66X	0.50X	0.33X	0.25X	0.13X	0.10X	0.08X
Field of View, 1/2" Sensor Horiz	9.7mm	12.8mm	19.4mm	25.6mm	49.2mm	64.0mm	80.0mm
Field of View, 1/3" Sensor Horiz	7.3mm	9.6mm	14.5mm	19.2mm	36.9mm	48.0mm	60.0mm

Working Distance	122mm	165mm	213mm	396mm	515mm	640mm
Primary Magnification	0.50X	0.33X	0.25X	0.13X	0.10X	0.08X
Field of View, 1/2" Sensor Horiz	12.8mm	19.4mm	25.6mm	51.2mm	64.0mm	80.0mm
Field of View, 1/3" Sensor Horiz	9.6mm	14.5mm	19.2mm	38.4mm	48.0mm	60.0mm