

[See all 13 Products in Family](#)

# ISDF 05-D to Flying Lead Cable, 2m

See More by [Teledyne DALSA](#)



Stock **#28-685** **1 In Stock**

-

1

+

₹4,089

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | ₹4,089 each                   |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

| General                           |                      |
|-----------------------------------|----------------------|
| G5-AIOC-BLUNT2M                   | Model Number:        |
| Teledyne DALSA                    | Manufacturer:        |
| Hardware & Interface Connectivity |                      |
|                                   | Length of Cable (m): |

|                                     |                             |
|-------------------------------------|-----------------------------|
| ISDF-05-D to Flying Lead            | Connector:                  |
| Regulatory Compliance               |                             |
| <a href="#">View</a>                | Certificate of Conformance: |
| China                               | Country of Origin:          |
| Edmund Optics India Private Limited | Imported By:                |

## Product Details

- Up to 67.10 MP Resolution with Framerates up to 18.50FPS
- Supports Trigger-to-Image Reliability (T2IR) Framework
- Compact (44 x 59 x 59mm), M42-Mbunt, Lightweight, and Robust All Metal Design



Teledyne DALSA Genie™ Nano 10GigE Cameras are designed with the 10GBASE-T (10GigE) Ethernet Interface and can also run at ethernet link speeds of 1, 2.5, or 5GigE. These M42-mount cameras are available with either the Teledyne e2v Emerald 36M sensor featuring a 1.4" format or the Teledyne e2v Emerald 67M sensor which features an APS-C format. Genie™ Nano cameras support Sopera LT SDKs and 3rd Party GenICam compliant SDKs allowing for upgrading current systems without changing application software. Teledyne DALSA Genie™ Nano 10GigE Cameras support the Trigger-to-Image Reliability (T2IR) framework which is a combination of hardware and software features that work together at a system level to help improve the reliability and reduce the downtime of imaging systems. These cameras are ideal for applications involving Electronics Manufacturing Inspection, Intelligent Traffic Systems, and Aerial Imaging.

**Sopera LT** is a free image acquisition and control software development toolkit (SDK) for Teledyne DALSA'S 1D cameras / 2D cameras / 3D Laser Profiler cameras and frame grabbers. Hardware independent in nature, Sopera LT offers a rich development ecosystem for machine vision OEMs and system integrators. Sopera LT supports image acquisition from cameras and frame grabbers based on machine vision standards including GigE Vision™, CameraLink®, CameraLink HS™, CoaXpress®, and USB3 Vision™.