

KC Objective IF-1



IF-Series Objectives (photo shows IF-1,IF-2, IF-3, IF-3.5, and IF-4), all sold separately

Stock **#53-781** [CONTACT US](#)

1 MRP ₹48,746

Price inclusive of all taxes

ADD TO CART

Volume Pricing

Qty 1+	₹48,746 each
Need More?	Request Quote

Product Downloads

General

Lens Accessory **Type:**

Physical & Mechanical Properties

19.50 **Length (mm):**

31.3 **Maximum Diameter (mm):**

Regulatory Compliance

Compliant RoHS 2015:

Compliant Reach 224:

View Certificate of Conformance:

United States Country of Origin:

Imported By:
 Edmund Optics India Private Limited
 267, Greystone Building, Second Floor,
 6th Cross Rd, Binnamangala,
 Stage 1, Indiranagar, Bengaluru,
 Karnataka, India 560038
 Phone: +91- 80-6845 0000

Product Details

- Telephoto, Macroscopic or Microscope Capability
- Focuses from Infinity to 63mm (with IF Objectives)
- Objectives Available to Provide Smaller FOVs and WDs

Designed to meet demanding imaging applications, the KC (with all 5 objectives) microscope lens provides primary magnification from 0.10-3.0X. Optional adapters for [Mitutoyo](#) and [Achromid™](#) infinity-corrected objectives and RMS objectives allow the KC to be used as a conventional microscope, without the bulk of traditional microscope bodies or inconvenience of adapting conventional microscopes to video cameras.


This microscope lens was designed as a gauging lens, with both large working distance and high magnification. Suitable for both off-line quality control and on-line inspection in production, especially for measurement and flaw inspection. [LDL](#) and LFA adapters thread onto C-Mount. LFA provides coverage for large format cameras (F-Mount adapter included, 24 x 36mm max sensor). Interchangeable objectives thread onto main body.

A [fiber optic illuminator](#) and a [ring light guide](#) are also recommended when using the IF4 objective. A coaxial attachment, [#56-191](#) can be used for applications requiring coaxial illumination.

Motorized InFocus™ KC Video Lens

The motorized KC lens comes complete with encased focus DC Gear-motor with rubber o-ring belt drive and bracket, CE analog control unit, motor/controller cable, and CE universal power supply (110V and 220V operation). The control unit allows the user to vary focus as well as the speed and direction at which focusing occurs.

Technical Information



Objective	IF1	IF2	IF3	IF3.5	IF4
Primary Magnification	0.36 - 0.75X	0.51 - 0.91X	0.80 - 1.28X	1.80 - 2.29X	2.29 - 2.98
Field of View (1/2" Sensor / Horiz.)	18 - 8mm	12.5 - 7mm	8 - 5mm	3.55 - 2.8mm	2.8 - 2.15mm
Working Distance (mm)	490 - 272	343 - 220	213 - 156	100 - 83	73 - 63

Note: Main body is required for these objectives.