

[See all 7 Products in Family](#)

Lightpath 7100350 | 15mm FL, f/1.0, Thermal Imaging Lens Assembly

See More by [Lightpath®](#)



Stock #15-689 CLEARANCE **16 In Stock**

MRP ₹26,938

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹26,938 each
Need More?	Request Quote

Product Downloads

General

Compatible Window:
 Thickness: 0.70mm
 Material: Si

Lightpath Lens Code:
 7100350

Physical & Mechanical Properties

Clear Aperture CA (mm):
 15.10

Construction:

Length (mm):
18.67

Front Diameter (mm):
24.00

Optical Properties

Effective Focal Length EFL (mm):
15.00

Substrate:
Black Diamond™ BD-6

f#:
1.0

Coating:
BBAR (8000-12000nm)

Wavelength Range (nm):
8000 - 12000

Coating Specification:
R_{avg} < 0.75% @ 8000 - 12,000nm

Index of Refraction (n_d) @ 10μm:
2.7816

Index of Refraction (n_d) @ 14μm:
2.7683

Index of Refraction (n_d) @ 4μm:
2.7978

Working Distance (mm):
11.24

Sensor

Recommended Detector Format (H x V/Pixel Size):
384 x 288 / 17μm

Threading & Mounting

Mounting Threads:
M25 x 0.5

Thread Length (mm):
7.00

Material Properties

Coefficient of Thermal Expansion CTE (10⁻⁶/°C):
22.5

Thermo-optic coefficient dn/dT:
30.5 x 10⁻⁶ @ 10μm

Regulatory Compliance

RoHS 2015:
Compliant

Certificate of Conformance:
[View](#)

Reach 233:
Compliant

Country of Origin:
China

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Precision Molded Chalcogenide Lenses
- Compact Designs for Thermal Imaging Cameras
- Focal Lengths from 2.7 to 24mm

Lightpath® Thermal Imaging Assemblies are a cost-effective alternative to diamond turned infrared lenses for applications in the mid-wave infrared (MMR) or long-wave infrared (LWR). These lenses are molded from BD6™, a chalcogenide glass that offers high transmission from 1 to 15μm and is also optically athermalized from -40 to +85°C. These lenses feature a broadband antireflection coating from 8 to 12μm and are mounted in compact black anodized aluminum housings that are threaded to allow for adjustable focus. Lightpath Thermal Imaging Assemblies are ideal for medical diagnostics, gas sensing, thermography, thermal imaging, security, and manufacturing process control applications. Lenses with focal lengths from 2.7 to 24mm are available, covering detector sizes from 80 x 80 to 640 x 480 pixels.