

[See all 15 Products in Family](#)

Line Pattern Flat Light LFX3-100SW-PT-B

See More by [CCS](#)



Stock #21-824 **1 In Stock**

1 MRP ₹2,95,767

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹2,95,767 each
Need More?	Request Quote

Product Downloads

General

Model Number:
LFX3-100SW-PT-B

Type of Illumination:
LED Illuminator

Manufacturer:
CCS

Geometry:
Flat Light

Illumination Mode:

Constant

Physical & Mechanical Properties

Dimensions (mm):
W 143 mm x D 143 mm x H 13.1 mm

Weight (g):
400

Optical Properties

Color:
White

Electrical

Power Consumption (W):
23

Hardware & Interface Connectivity

Input Voltage (V):
24

Power Supply:
Power Supply Required and Sold Separately.
USA: [#73-491](#)
Europe: [#73-491](#)
Japan: [#89-513](#)
Korea: [#33-773](#)
China: [#73-491](#)

Environmental & Durability Factors

Color Temperature (K):
6800

Regulatory Compliance

RoHS 2015:
[Exempt](#)

Reach 224:
[Contains SVHC\(s\)](#)

Certificate of Conformance:
[View](#)

Country of Origin:
United States

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91-80-6845 0000

Product Details


- Detect Imperfections on Reflective Surfaces
- Line Pattern Projected Through Light Guiding Diffusion Plate
- Multiple Wavelengths and Working Distances Available

CCS Coaxial Line Pattern Flat Lights feature a line pattern on the surface of a light guiding diffusion plate which allows for the detection of minute bumps and dents on reflective surfaces. When integrated into a machine vision system, the image of the reflected line pattern highlights defects by breaking the continuity of the surface and distorting the line pattern. These flat lights are available with two pitch options, 1mm for shorter working distances and 2mm for longer working distances. CCS Coaxial Line Pattern Flat Lights are ideal for inspection of reflective surfaces such as mirrors, metal sheets, glass surfaces, and reflective films.

Technical Information

Two types of line patterns available

Select one to match your inspection conditions.



Example configuration (LFX3-100-PT)

