

[See all 22 Products in Family](#)

## 25mm Dia., 127° Diffusion Angle, Linear Batwing Diffuser



Angle Bending Diffuser

Stock **#28-929** **20+ In Stock**

1  MRP ₹8,273

Price inclusive of all taxes

**ADD TO CART**

### Volume Pricing

Qty 1-9	₹8,273 each
Qty 10-25	₹7,415 each
Qty 26-49	₹6,608 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

Linear Batwing Diffuser **Type:**

Glossy, specularly-reflective side should face incident light for optimal performance. **Note:**

### Physical & Mechanical Properties

25.00 ±0.13 **Diameter (mm):**

1.75 ±0.36 **Thickness (mm):**

## Optical Properties

127 **Diffusing Angle (°):**

PMMA **Substrate:**

## Environmental & Durability Factors

-34 to +70 **Operating Temperature (°C):**

## Regulatory Compliance

[View](#) **Certificate of Conformance:**

United States **Country of Origin:**

**Imported By:**  
Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91-80-6845 0000

## Product Details

- High Efficiency, Angle Bending, Batwing, and Elliptical Configurations Available
- Transmission Efficiency >88%
- Low-Cost, High-Performance Diffusers

Beam Shaping Diffusers provide an even distribution of LED and fluorescent illumination in a variety of configurations including High Efficiency, Angle Bending, Batwing, and Elliptical while maintaining a high transmission efficiency of >88%. The high efficiency and angle bending configurations provide even light distribution whereas the batwing and elliptical configurations distribute light according to their respective geometries. Beam Shaping Diffusers feature diffusing angles between 8° - 127° and are available as 25mm diameter unmounted optics with a thickness of no more than 1.75mm, enabling easy integration into a variety of bench top or OEM applications. These Diffusers are ideal for applications where excellent depixelation, angle control, color mixing, and color uniformity are required.

## Technical Information

BEAM SHAPING DIFFUSERS

Type of Diffuser	Description	Diffusion Example
High Efficiency Diffuser	High Efficiency Diffusers are ideal for providing even illumination in LED applications. They provide excellent depixelation, angle control, and color uniformity.	
Linear Batwing Diffuser	Linear Batwing Diffusers diffuse light in a batwing distribution, ideal for eliminating central hotspots from a light source. Incident light should be from the glossy, specularly-reflective side of these diffusers for optimal performance. Light distributions may vary significantly depending on the light source used.	
Elliptical Diffuser	Elliptical Diffusers diffuse light asymmetrically, creating an elliptical light pattern. The diffusing angles are specified as W x L.	
Angle Bending Diffuser	Angle Bending Diffusers both redirect and diffuse incident light, ideal for creating diffuse lighting in space-constrained environments.	