

[See all 13 Products in Family](#)

# White, Low-Angle Square Light FPQ3-120SW

See More by [CCS](#)



Stock #21-813 **1 In Stock**

- 1 + MRP ₹2,02,311

**!** Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1+	₹2,02,311 each
Need More?	<a href="#">Request Quote</a>

## Product Downloads

### General

FPQ3-120SW **Model Number:**

LED Illuminator **Type of Illumination:**

CCS **Manufacturer:**

Low-Angle Square Light **Geometry:**

**Illumination Mode:**

Constant

## Physical & Mechanical Properties

**Dimensions (mm):**  
W 120 mm x D 120 mm x H 30 mm

**Weight (g):**  
220

## Optical Properties

**Color:**  
White

## Electrical

**Power Consumption (W):**  
27

## Hardware & Interface Connectivity

**Input Voltage (V):**  
24

**Power Supply:**  
Power Supply Required and Sold Separately.  
USA: [#73-491](#)  
Europe: [#73-491](#)  
Japan: [#89-513](#)  
Korea: [#33-773](#)  
China: [#73-491](#)

## Environmental & Durability Factors

**Color Temperature (K):**  
6000

## Regulatory Compliance

**RoHS 2015:**  
[Exempt](#)

**Reach 224:**  
[Contains SVHC\(s\)](#)

**Certificate of Conformance:**  
[View](#)

**Country of Origin:**  
United States

**Imported By:**  
Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Product Details

- Improved Inspection of Rectangular and Square Objects vs. Ring Lights
- Low-Angle Lighting from Four Directions
- Ideal for Inspection of Food Packaging and PCB's

CCS Low-Angle Square LED Illuminators provide uniform diffuse illumination from a low angle in four directions. This low-angle square design helps to prevent glare and enables the detection of outlines and corners which is difficult to achieve with traditional ring lights. These lights feature mounting holes along the top and sides, allowing for flexibility with system installation. CCS Low-Angle Square LED Illuminators are ideal for embossed character recognition and inspection of square parts such as food packaging, circuit boards (PCB's), and print patterns.

**Note:** Power supply [#66-855](#) is required and sold separately.

## Technical Information

### Imaging Examples for the FPQ3-100X50 Light Unit

Illumination from a low angle clearly highlights the outline of workpieces.

