

Low Order Ultra High LDT Waveplate $\lambda/2$ 532nm 25.4mm Dia



Stock **#70-198** **4 In Stock**

-

1

+

₹64,226

ADD TO CART

Volume Pricing	
Qty 1+	₹64,226 each
Need More?	Request Quote

Product Downloads

General

Crystalline Waveplate

Type:

Physical & Mechanical Properties

>20

Clear Aperture CA (mm):

25.40 +0.00/-0.25

Diameter (mm):

Air-Spaced

Construction:

Parallelism (arcsec):

Optical Properties	
R _{avg} <0.1% on each surface	Coating:
532	Design Wavelength DWL (nm):
Crystal Quartz	Substrate: ☐
$\lambda/2$	Retardance:
20-10	Surface Quality:
< $\lambda/10$ @ 632.8mm	Transmitted Wavefront, P-V:
< $\lambda/500$ @ 20C	Retardance Tolerance:
>20J/cm² @ 532nm;10ns;10 Hz	Damage Threshold, By Design: ☐

Threading & Mounting	
6.00 +0.00/-0.25	Mount Thickness (mm):

Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:
Lithuania	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- High Laser Damage Threshold at Common Laser Processing Wavelengths
- $\lambda/500$ Retardance Tolerance
- Ideal for Material Machining Applications

Precision Waveplates for Laser Processing offer an exceptional damage threshold making them ideal for material processing and other high energy applications. These waveplates feature a premium retardance tolerance of $\lambda/500$, enabling their use in sensitive applications requiring high precision and stability. Designed as zero order, these waveplates allow for a greater than $\pm 1\%$ wavelength deviation due to their increased bandwidth and lower sensitivity to temperature change. Precision Waveplates for Laser Processing are available in 25.4 and 50.8mm diameters and are designed for commonly used material machining wavelengths of 532, 1030, and 1064nm. The waveplates designed for use with Nd:YAG laser wavelengths feature damage thresholds up to 35J/cm2 @ 1064nm with 10ns pulses while the waveplates designed for Yb:YAG feature damage thresholds up to 0.5 J/cm² @ 1030 nm with 200fs pulses.