


[See all 27 Products in Family](#)

LUCID Vision Labs Atlas™ ATL120S-MC, Sony IMX253, 12.3MP, Monochrome Camera

See More by [LUCID Vision Labs™](#)



LUCID Vision Labs Atlas™ Power over Ethernet (PoE) 5GBASE-T (5GigE) Cameras

Stock **#13-733** [CONTACT US](#)

[Similar Cameras](#)

-

1

+

 ₹3,39,840

 Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹3,39,840 each
Need More?	Request Quote

Product Downloads

Monochrome	Spectrum:
General	
Monochrome Camera	Type:
ATL120S-MC	Model Number:
Lucid Vision Labs	Manufacturer:

Atlas™	Camera Series:
Physical & Mechanical Properties	
55 x 55 x 70 (excludes connectors and lens mount)	Dimensions (mm):
240	Weight (g):
Full	Housing:
Sensor	
380MB	Image Buffer:
1.1"	Sensor Format:
12.30	Resolution (Megapixels):
42.00	Frame Rate (fps):
4,096 x 3,000	Pixels (H x V):
3.45 x 3.45	Pixel Size, H x V (µm):
14.13 x 10.35	Sensing Area, H x V (mm):
Sony IMX253	Imaging Sensor:
Progressive Scan CMOS	Type of Sensor:
Global	Shutter Type:
8/10/12 Bit	Pixel Depth:
30µs - 10s	Exposure Time:
71.2	Dynamic Range (dB):
GigE Vision v2.0	Machine Vision Standard:
Electrical	
7 (External Power Supply) 8 (PoE)	Power Consumption (W):
Hardware & Interface Connectivity	
5GigE (PoE)	Interface:
5GigE, M12	Connector:
Power Supply Required and Sold Separately: USA: #18-364 Europe: #18-364 Japan: #18-364 Korea: Not Available China: #18-364	Power Supply:
1 opto-isolated input, 1 opto-isolated output, 2 non-isolated bi-directional ports	GPIOs:
Hardware Trigger (GPIO), Software Trigger, or PTP (IEEE 1588)	Synchronization:
Back Panel	Interface Port Orientation:
8-pin MB	GPIO Connector Type:
Threading & Mounting	
C-Mount	Mount:
¼-20 with Tripod Mount Adapter #13-751	Mounting Threads:
Environmental & Durability Factors	
-20 to +55	Operating Temperature (°C):

	Storage Temperature (°C):
-30 to +60	

Regulatory Compliance

	Certificate of Conformance:
View	
	Country of Origin:
Canada	
	Imported By:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	

Product Details

- 5GBASE-T (5GigE) Ethernet Interface
- 2.8 to 31.4 Megapixel Sensors
- Compact 55 x 55 x 70mm Design
- TFL-Mount Compatible with [TECHSPEC® CA Series FFL Lenses](#)

LUCID Vision Labs Atlas™ Power over Ethernet (PoE) 5GBASE-T (5GigE) Cameras have a small footprint and feature large format, high resolution sensors with up to 31.4MP at 17.9fps. During manufacturing, their imaging sensors are actively aligned to minimize sensor tilt and rotation, resulting in sharp and crisp images even in the corners. The 5GigE Ethernet interface provides up to 5X faster speeds than GigE for applications requiring high bandwidth. These cameras also feature a TFL-Mount that is easily adaptable to F-Mount. LUCID Vision Labs Atlas Power over Ethernet (PoE) 5GBASE-T (5GigE) Cameras are ideal for industrial applications including [factory automation](#), autonomous robotics, and biometrics.