

[See all 11 Products in Family](#)

LUCID Vision Labs Helios™2+ Time of Flight (ToF) Camera

See More by [LUCID Vision Labs™](#)



LUCID Helios™2 Time of Flight (ToF) Cameras

Stock **#23-920** [CONTACT US](#)

- 1 + MRP ₹1,90,629

i Price inclusive of all taxes

ADD TO CART

Volume Pricing

Qty 1+	₹1,90,629 each
Need More?	Request Quote

Product Downloads

Monochrome

Spectrum:

General

Monochrome Camera

Type:

HTP003S-001

Model Number:

Lucid Vision Labs

Manufacturer:

Helios™

Camera Series:

Contents of Kit:

-

Physical & Mechanical Properties

Dimensions (mm):

60 x 60 x 77.5 (excludes connectors and lens mount)

Weight (g):

398

Housing:

Full

Sensor

Image Buffer:

Not Specified

Sensor Format:

1/2"

Resolution (Megapixels):

0.30

Frame Rate (fps):

30.00 FPS (Normal)
10 FPS (HDR)
103 FPS (High-Speed)

Pixels (H x V):

640 x 480

Pixel Size, H x V (µm):

10 x 10

Sensing Area, H x V (mm):

0.64 x 0.48

Imaging Sensor:

Sony DepthSense IMX556

Type of Sensor:

Progressive Scan CMOS

Shutter Type:

Global

Pixel Depth:

8/12/16 bit

Exposure Time:

62.5 µs, 250 µs, or 1000 µs

Dynamic Range (dB):

Standard and HDR Modes

Machine Vision Standard:

GigE Vision v2.0

Electrical

Power Consumption (W):

12 - 30

Hardware & Interface Connectivity

Interface:

GigE (PoE+)

Connector:

GigE, M12

Power Supply:

Power over Ethernet (PoE) or via GPIO with 12-24VDC Power Supply

GPIOs:

1 opto-isolated input, 1 opto-isolated output, 2 non-isolated bi-directional ports

Synchronization:

Hardware Trigger (GPIO), Software Trigger, or PTP (IEEE 1588)

Interface Port Orientation:

Back Panel

GPIO Connector Type:

8-pin MB

Threading & Mounting

Mount:

No Lens Mount

Mounting Threads:

N/A

Environmental & Durability Factors

Operating Temperature (°C):

-20° to 50°C

Storage Temperature (°C):

-20° to 50°C

Regulatory Compliance

Certificate of Conformance:

[View](#)

Country of Origin:

Canada

Imported By:

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Ideal for Robotics and Automation Applications
- IP67 Rated 3D Cameras
- Available Kits Feature 3D and 2D RGB Solutions

LUCID Helios™2 Time of Flight (ToF) Cameras are 3D cameras featuring Sony's DepthSense sensor, engineered for high performance operation in industrial environments. Built for demanding 24/7 environments, these cameras are ideal for robotics, 3D inspection, advanced material handling, sorting and pick and place applications. LUCID Helios™2 Time of Flight (ToF) Cameras feature enhanced calibration between the VCSELs and sensor timing, resulting in higher 3D detail, along with improved edge detection to reduce flying pixels and overall noise. For an even higher performance option, the Helios™2+ offers high dynamic range and high-speed modes for precise and quick analyzation. Available kits feature a Helios™2 ToF Camera, 3.2MP Triton Camera, lens tubes, cables, and accessories required for creating dust proof, water-resistant color point clouds.

;