

[See all 40 Products in Family](#)

# LUCID Vision Labs Triton2™ TRT024G-CC, Gpixel GMAX4002C, 2.4MP, Color Camera

See More by [LUCID Vision Labs™](#)



LUCID Vision Labs Triton2™ 2.5GigE Power over Ethernet (PoE) Cameras - Front



Stock #72-918 [CONTACT US](#)

- 1 + MRP ₹77,290

Price inclusive of all taxes

**ADD TO CART**

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | ₹77,290 each                  |
| Need More?     | <a href="#">Request Quote</a> |

## Product Downloads

Color **Spectrum:**

## General

Color Camera **Type:**

TRT024G-CC **Model Number:**

Lucid Vision Labs **Manufacturer:**

Triton2™ **Camera Series:**

## Physical & Mechanical Properties

44.0 x 29.0 x 45.3 (excludes connectors and lens mount) **Dimensions (mm):**

90 **Weight (g):**

Full **Housing:**

## Sensor

128MB **Image Buffer:**

1/1.7" **Sensor Format:**

2.40 **Resolution (Megapixels):**

107.20 **Frame Rate (fps):**

2,048 x 1,200 **Pixels (H x V):**

4.00 x 4.00 **Pixel Size, H x V (µm):**

8.19 x 4.80 **Sensing Area, H x V (mm):**

Gpixel GMAX4002C **Imaging Sensor:**

Progressive Scan CMOS **Type of Sensor:**

Global **Shutter Type:**

12 bit **Pixel Depth:**

11.06µs to 10s **Exposure Time:**

48.0 **Dynamic Range (dB):**

GigE Vision v2.0 **Machine Vision Standard:**

## Electrical

4.5 (External Power Supply) 5.0 (PoE) **Power Consumption (W):**

## Hardware & Interface Connectivity

2.5GigE (PoE) **Interface:**

2.5GigE, GigE, M12 **Connector:**

Power Supply Required and Sold Separately.  
USA: [#18-364](#)  
Europe: [#18-365](#)  
Japan: [#18-364](#)  
Korea: Not Available  
China: [#18-365](#) **Power Supply:**

1 opto-isolated input, 1 opto-isolated output, 2 non-isolated bi-directional ports **GPIOs:**

Hardware Trigger (GPIO), Software Trigger, or PTP (IEEE 1588) **Synchronization:**

Back Panel **Interface Port Orientation:**

8-pin MB **GPIO Connector Type:**

## Threading & Mounting

C-Mount **Mount:**

1/4-20 with Tripod Mount Adapter **Mounting Threads:**

## Environmental & Durability Factors

**Operating Temperature (°C):**  
-20 to +55

**Storage Temperature (°C):**  
-30 to +60

---

## Regulatory Compliance

**Certificate of Conformance:**  
[View](#)

---

**Country of Origin:**  
Canada

**Imported By:**  
Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

---

## Product Details

- 2.5GBASE-T (2.5GigE) Ethernet Interface
- 5.0 to 24.50 MegaPixel Sensors
- Compact 44 x 29 x 45.3mm Form Factor
- IP67 Protection with Optional Lens Tubes

LUCID Vision Labs Triton2™ 2.5GigE Power over Ethernet (PoE) Cameras provide data transfer speeds of 2.5GigE enabling high frame rates at increased resolutions. Featuring an actively aligned image sensor, these cameras are designed to minimize sensor tilt and rotation and ensure alignment of the image sensor to the lens optical axis. For harsh environments with dust or water, accessory lens tubes are available to ensure an IP67 rating. LUCID Vision Labs Triton2™ 2.5GigE Power over Ethernet (PoE) Cameras feature excellent thermal management with a wide operating temperature range from -20°C to 55°C. These cameras are ideal for automotive, process control, and food and beverage applications.

---

;