

[See all 40 Products in Family](#)

LUCID Vision Labs Triton2™ TRT028S-MC, Sony IMX429, 2.8MP, Monochrome Camera

See More by [LUCID Vision Labs™](#)



LUCID Vision Labs Triton2™ 2.5GigE Power over Ethernet (PoE) Cameras - Front



Stock #72-921 **1 In Stock**

MRP ₹70,623

Price inclusive of all taxes

ADD TO CART

Volume Pricing

Qty 1+	₹70,623 each
Need More?	Request Quote

Product Downloads

Spectrum:
Monochrome

General

Type:
Monochrome Camera

Model Number:
TRT028S-MC

Lucid Vision Labs

Manufacturer:

Triton2™

Camera Series:

Physical & Mechanical Properties

Dimensions (mm):

44.0 x 29.0 x 45.3 (excludes connectors and lens mount)

Weight (g):

90

Housing:

Full

Sensor

Image Buffer:

128MB

Sensor Format:

2/3"

Resolution (Megapixels):

2.80

Frame Rate (fps):

64.90

Pixels (H x V):

1,936 x 1,464

Pixel Size, H x V (µm):

4.50 x 4.50

Sensing Area, H x V (mm):

8.71 x 6.59

Imaging Sensor:

Sony IMX429

Type of Sensor:

Progressive Scan CMOS

Shutter Type:

Global

Pixel Depth:

12 bit

Exposure Time:

15.22µs to 10s

Dynamic Range (dB):

48.0

Machine Vision Standard:

GigE Vision v2.0

Electrical

Power Consumption (W):

4.5 (External Power Supply) 5.0 (PoE)

Hardware & Interface Connectivity

Interface:

2.5GigE (PoE)

Connector:

2.5GigE, GigE, M12

Power Supply:

Power Supply Required and Sold Separately.

USA: [#18-364](#)

Europe: [#18-365](#)

Japan: [#18-364](#)

Korea: Not Available

China: [#18-365](#)

GPIOs:

1 opto-isolated input, 1 opto-isolated output, 2 non-isolated bi-directional ports

Synchronization:

Hardware Trigger (GPIO), Software Trigger, or PTP (IEEE 1588)

Interface Port Orientation:

Back Panel

GPIO Connector Type:

8-pin MB

Threading & Mounting

Mount:

C-Mount

Mounting Threads:

1/4-20 with Tripod Mount Adapter

Environmental & Durability Factors

Operating Temperature (°C):
-20 to +55

Storage Temperature (°C):
-30 to +60

Regulatory Compliance

Certificate of Conformance:
[View](#)

Country of Origin:
Canada

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- 2.5GBASE-T (2.5GigE) Ethernet Interface
- 5.0 to 24.50 MegaPixel Sensors
- Compact 44 x 29 x 45.3mm Form Factor
- IP67 Protection with Optional Lens Tubes

LUCID Vision Labs Triton2™ 2.5GigE Power over Ethernet (PoE) Cameras provide data transfer speeds of 2.5GigE enabling high frame rates at increased resolutions. Featuring an actively aligned image sensor, these cameras are designed to minimize sensor tilt and rotation and ensure alignment of the image sensor to the lens optical axis. For harsh environments with dust or water, accessory lens tubes are available to ensure an IP67 rating. LUCID Vision Labs Triton2™ 2.5GigE Power over Ethernet (PoE) Cameras feature excellent thermal management with a wide operating temperature range from -20°C to 55°C. These cameras are ideal for automotive, process control, and food and beverage applications.

;