

[See all 40 Products in Family](#)

LUCID Vision Labs Triton2™ TRT064S-MC, Sony IMX178, 6.3MP, Monochrome Camera

See More by [LUCID Vision Labs™](#)



LUCID Vision Labs Triton2™ 2.5GigE Power over Ethernet (PoE) Cameras - Front



Stock #72-925 **1 In Stock**

1 MRP ₹57,879

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹57,879 each
Need More?	Request Quote

Product Downloads

Monochrome	Spectrum:
General	
Monochrome Camera	Type:
TRT064S-MC	Model Number:

Lucid Vision Labs **Manufacturer:**

Triton2™ **Camera Series:**

Physical & Mechanical Properties

44.0 x 29.0 x 45.3 (excludes connectors and lens mount) **Dimensions (mm):**

90 **Weight (g):**

Full **Housing:**

Sensor

128MB **Image Buffer:**

1/1.8" **Sensor Format:**

6.30 **Resolution (Megapixels):**

42.80 **Frame Rate (fps):**

3,072 x 2,048 **Pixels (H x V):**

2.40 x 2.40 **Pixel Size, H x V (µm):**

7.37 x 4.92 **Sensing Area, H x V (mm):**

Sony IMX178 **Imaging Sensor:**

Progressive Scan CMOS **Type of Sensor:**

Rolling **Shutter Type:**

12 bit **Pixel Depth:**

13.344µs to 10s **Exposure Time:**

48.0 **Dynamic Range (dB):**

GigE Vision v2.0 **Machine Vision Standard:**

Electrical

4.5 (External Power Supply) 5.0 (PoE) **Power Consumption (W):**

Hardware & Interface Connectivity

2.5GigE (PoE) **Interface:**

2.5GigE, GigE, M12 **Connector:**

Power Supply Required and Sold Separately:
USA: [#18-364](#)
Europe: [#18-365](#)
Japan: [#18-364](#)
Korea: Not Available
China: [#18-365](#) **Power Supply:**

1 opto-isolated input, 1 opto-isolated output, 2 non-isolated bi-directional ports **GPIOs:**

Hardware Trigger (GPIO), Software Trigger, or PTP (IEEE 1588) **Synchronization:**

Back Panel **Interface Port Orientation:**

8-pin M8 **GPIO Connector Type:**

Threading & Mounting

C-Mount **Mount:**

1/4-20 with Tripod Mount Adapter **Mounting Threads:**

Environmental & Durability Factors

Operating Temperature (°C):

-20 to +55

Storage Temperature (°C):

-30 to +60

Regulatory Compliance

Certificate of Conformance:

[View](#)

Country of Origin:

Canada

Imported By:

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- 2.5GBASE-T (2.5GigE) Ethernet Interface
- 5.0 to 24.50 MegaPixel Sensors
- Compact 44 x 29 x 45.3mm Form Factor
- IP67 Protection with Optional Lens Tubes

LUCID Vision Labs Triton2™ 2.5GigE Power over Ethernet (PoE) Cameras provide data transfer speeds of 2.5GigE enabling high frame rates at increased resolutions. Featuring an actively aligned image sensor, these cameras are designed to minimize sensor tilt and rotation and ensure alignment of the image sensor to the lens optical axis. For harsh environments with dust or water, accessory lens tubes are available to ensure an IP67 rating. LUCID Vision Labs Triton2™ 2.5GigE Power over Ethernet (PoE) Cameras feature excellent thermal management with a wide operating temperature range from -20°C to 55°C. These cameras are ideal for automotive, process control, and food and beverage applications.