

[See all 59 Products in Family](#)

# LUCID Vision Labs Triton™ TRI032S-MC, Sony IMX265, 3.2MP, Monochrome Camera

See More by [LUCID Vision Labs™](#)



LUCID Vision Labs Triton™ Power over Ethernet (PoE) Cameras



Stock **#13-715** [CONTACT US](#)

[Similar Cameras](#)

⊖ 1 ⊕ MRP ₹55,224

● Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1+	₹55,224 each
Need More?	<a href="#">Request Quote</a>

## Product Downloads

**Spectrum:**  
Monochrome

## General

**Type:**  
Monochrome Camera

**Model Number:**  
TRI032S-MC

Lucid Vision Labs  
Triton™

**Manufacturer:**  
**Camera Series:**

## Physical & Mechanical Properties

29 x 29 x 45 (excludes connectors and lens mount)  
67

**Dimensions (mm):**  
**Weight (g):**

Full

**Housing:**

## Sensor

128MB  
1/1.8"

**Image Buffer:**  
**Sensor Format:**

3.20  
38.00

**Resolution (Megapixels):**  
**Frame Rate (fps):**

2,048 x 1,536  
3.45 x 3.45

**Pixels (H x V):**  
**Pixel Size, H x V (µm):**

7.07 x 5.3  
Sony IMX265

**Sensing Area, H x V (mm):**  
**Imaging Sensor:**

Progressive Scan CMOS  
Global

**Type of Sensor:**  
**Shutter Type:**

12 bit  
30µs - 10s

**Pixel Depth:**  
**Exposure Time:**

71.78  
GigE Vision v2.0

**Dynamic Range (dB):**  
**Machine Vision Standard:**

## Electrical

2.5 (External Power Supply)  
3.1 (PoE)

**Power Consumption (W):**

## Hardware & Interface Connectivity

GigE (PoE)  
GigE, M12

**Interface:**  
**Connector:**

Power Supply Required and Sold Separately.  
USA: [#18-364](#)  
Europe: [#18-364](#)  
Japan: [#18-364](#)  
Korea: Not Available  
China: [#18-364](#)

**Power Supply:**

1 opto-isolated input, 1 opto-isolated output, 2 non-isolated bi-directional ports

**GPIOs:**

Hardware Trigger (GPIO), Software Trigger, or PTP (IEEE 1588)

**Synchronization:**

Back Panel

**Interface Port Orientation:**

8-pin M8

**GPIO Connector Type:**

## Threading & Mounting

C-Mount

**Mount:**

1/4-20 with Tripod Mount Adapter [#11-474](#)

**Mounting Threads:**

## Environmental & Durability Factors

---

**Operating Temperature (°C):**  
-20 to +55

**Storage Temperature (°C):**  
-30 to +60

---

## Regulatory Compliance

**Certificate of Conformance:**  
[View](#)

---

**Country of Origin:**  
Canada

**Imported By:**  
Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

---

## Product Details

- Compact 29 x 29 x 45mm Form Factor
- Global, Rolling, or Polarized CMOS Sensors
- IP67 Protection with Optional Lens Tubes

LUCID Vision Labs Triton™ GigE Power over Ethernet (PoE) Cameras provide exceptional price performance in a compact 29 x 29mm form factor. These cameras are available with Sony's Pregius™ and Starvis™ imaging sensors with up to 24.5 megapixels of resolution, as well as Sony's polarized sensor. Each imaging sensor is actively aligned during manufacturing, ensuring sharp and crisp images even in the corners. Using the accessory IP67 lens tubes (sold separately), LUCID Vision Labs Triton GigE Power over Ethernet (PoE) Cameras can operate in harsh environments where dust or water are present up to IP67 thresholds. Triton cameras are ideal for automotive, process control, and food and beverage applications.

---

;