

[See all 29 Products in Family](#)

LUCID Vision Labs™ Atlas ATP081S-CC, Sony IMX546, 8.1MP, IP67 Color Camera

See More by [LUCID Vision Labs™](#)



Stock #23-964 [CONTACT US](#)

- 1 + MRP ₹1,44,432

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹1,44,432 each
Need More?	Request Quote

Note: This item requires accessories for use | [Learn More](#)

Product Downloads

Color **Spectrum:**

General

Color Camera **Type:**

ATP081S-CC **Model Number:**

Lucid Vision Labs **Manufacturer:**

Atlas IP67 **Camera Series:**

Physical & Mechanical Properties

60 x 60 x 65 **Dimensions (mm):**

340 **Weight (g):**

Full **Housing:**

Sensor

380MB **Image Buffer:**

2/3" **Sensor Format:**

8.10 **Resolution (Megapixels):**

68.80 **Frame Rate (fps):**

2,840 x 2,840 **Pixels (H x V):**

2.74 x 2.74 **Pixel Size, H x V (μm):**

7.78 x 7.78 **Sensing Area, H x V (mm):**

Sony IMX546 **Imaging Sensor:**

Progressive Scan CMOS **Type of Sensor:**

Global **Shutter Type:**

8/10/12/16 Bit **Pixel Depth:**

8 μs to 10 s (Normal) / 2.31 μs to 2.47 μs (Short Mode) **Exposure Time:**

Not Specified **Dynamic Range (dB):**

GigE Vision v2.0 **Machine Vision Standard:**

Electrical

8W via PoE, 7W when powered externally **Power Consumption (W):**

Hardware & Interface Connectivity

5GigE (PoE) **Interface:**

5GigE, M12 **Connector:**

PoE (IEEE 802.3af), or 12-24 VDC external **Power Supply:**

1 opto-isolated input, 1 opto-isolated out, 2 non-isolated bi-directional ports **GPIOs:**

Hardware Trigger (GPIO), Software Trigger, or PTP (IEEE 1588) **Synchronization:**

Back Panel **Interface Port Orientation:**

8 pin M8 connector **GPIO Connector Type:**

Threading & Mounting

C-Mount **Mount:**

Environmental & Durability Factors

-20 to 55 **Operating Temperature ($^{\circ}\text{C}$):**

-30 to 60 **Storage Temperature ($^{\circ}\text{C}$):**

Regulatory Compliance

Certificate of Conformance:

[View](#)

Country of Origin:

Canada

Imported By:

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- IP67 Rated for Protection from Water Ingress, Dust and Dirt
- 5Gbase-T (5GigE) Ethernet Interface
- Supports Power over Ethernet (PoE), Simplifying Integration

LUCID Vision Labs Atlas IP67 5GigE Cameras are water ingress protected, industrial cameras designed for imaging applications requiring high bandwidth and performance in rugged environments. These cameras support the 5Gbase-T (5GigE) Ethernet interface and are Power over Ethernet (PoE), capable of 600 MB/s data transfer rates which allow for high resolution and frame rates. LUCID Vision Labs Atlas IP67 5GigE Cameras feature a C-mount and Active Sensor alignment for superior optical performance. These cameras offer a perfect balance of fast frame rates, compact size, industrial ruggedization, and an excellent price-performance ratio.

;