

[See all 30 Products in Family](#)

LUCID Vision Labs™ Atlas ATP081S-MC, Sony IMX546, 8.1MP, IP67 Monochrome Camera

See More by [LUCID Vision Labs™](#)



Stock **#23-963** 1 In Stock

-

1

+

₹1,36,000

ADD TO CART

Volume Pricing	
Qty 1+	₹1,36,000 each
Need More?	Request Quote

Note: This item requires accessories for use | [Learn More](#)

Product Downloads

Monochrome

Spectrum:

General

Monochrome Camera

Type:

ATP081S-MC

Model Number:

Lucid Vision Labs

Manufacturer:

Atlas IP67	Camera Series:
Physical & Mechanical Properties	
60 x 60 x 65	Dimensions (mm):
340	Weight (g):
Full	Housing:
Sensor	
380MB	Image Buffer:
2/3"	Sensor Format:
8.10	Resolution (Megapixels):
68.80	Frame Rate (fps):
2,840 x 2,840	Pixels (H x V):
2.74 x 2.74	Pixel Size, H x V (µm):
7.78 x 7.78	Sensing Area, H x V (mm):
Sony IMX546	Imaging Sensor:
Progressive Scan CMOS	Type of Sensor:
Global	Shutter Type:
8/10/12/16 Bit	Pixel Depth:
8 µs to 10 s (Normal) / 2.31 µs to 2.47 µs (Short Mode)	Exposure Time:
Not Specified	Dynamic Range (dB):
GigE Vision v2.0	Machine Vision Standard:
Electrical	
8W via PoE, 7W when powered externally	Power Consumption (W):
Hardware & Interface Connectivity	
5GigE (PoE)	Interface:
5GigE, M12	Connector:
PoE (IEEE 802.3af), or 12-24 VDC external	Power Supply:
1 opto-isolated input, 1 opto-isolated out, 2 non-isolated bi-directional ports	GPIOs:
Hardware Trigger (GPIO), Software Trigger, or PTP (IEEE 1588)	Synchronization:
Back Panel	Interface Port Orientation:
8 pin M8 connector	GPIO Connector Type:
Threading & Mounting	
C-Mount	Mount:
Environmental & Durability Factors	
-20 to 55	Operating Temperature (°C):
-30 to 60	Storage Temperature (°C):
Regulatory Compliance	
	Certificate of Conformance:

Country of Origin:	
Canada	
Imported By:	
Edmund Optics India Private Limited	

Product Details

- IP67 Rated for Protection from Water Ingress, Dust and Dirt
- 5Gbase-T (5GigE) Ethernet Interface
- Supports Power over Ethernet (PoE), Simplifying Integration

LUCID Vision Labs Atlas IP67 5GigE Cameras are water ingress protected, industrial cameras designed for imaging applications requiring high bandwidth and performance in rugged environments. These cameras support the 5Gbase-T (5GigE) Ethernet interface and are Power over Ethernet (PoE), capable of 600 MB/s data transfer rates which allow for high resolution and frame rates. LUCID Vision Labs Atlas IP67 5GigE Cameras feature a C-mount and Active Sensor alignment for superior optical performance. These cameras offer a perfect balance of fast frame rates, compact size, industrial ruggedization, and an excellent price-performance ratio.