

[See all 29 Products in Family](#)

# LUCID Vision Labs™ Atlas ATP204S-MC, Sony IMX541, 20.4MP, IP67 Monochrome Camera

See More by [LUCID Vision Labs™](#)



Stock #23-975 **1 In Stock**

- 1 + MRP ₹2,62,314

Price inclusive of all taxes

**ADD TO CART**

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | ₹2,62,314 each                |
| Need More?     | <a href="#">Request Quote</a> |

Note: This item requires accessories for use | [Learn More](#)

## Product Downloads

Monochrome **Spectrum:**

## General

Monochrome Camera **Type:**

ATP204S-MC **Model Number:**

**Manufacturer:**

Atlas IP67 **Camera Series:**

## Physical & Mechanical Properties

60 x 60 x 65 **Dimensions (mm):**

340 **Weight (g):**

Full **Housing:**

## Sensor

380MB **Image Buffer:**

1.1" **Sensor Format:**

20.40 **Resolution (Megapixels):**

27.40 **Frame Rate (fps):**

4,504 x 4,504 **Pixels (H x V):**

2.74 x 2.74 **Pixel Size, H x V ( $\mu\text{m}$ ):**

12.34 x 12.34 **Sensing Area, H x V (mm):**

Sony IMX541 **Imaging Sensor:**

Progressive Scan CMOS **Type of Sensor:**

Global **Shutter Type:**

8/10/12 Bit **Pixel Depth:**

10.74  $\mu\text{s}$  to 10 s (Normal) / 2.29  $\mu\text{s}$  to 2.46  $\mu\text{s}$  (Short Mode) **Exposure Time:**

Not Specified **Dynamic Range (dB):**

GigE Vision v2.0 **Machine Vision Standard:**

## Electrical

8W via PoE, 7W when powered externally **Power Consumption (W):**

## Hardware & Interface Connectivity

5GigE (PoE) **Interface:**

5GigE, M12 **Connector:**

PoE (IEEE 802.3af), or 12-24 VDC external **Power Supply:**

1 opto-isolated input, 1 opto-isolated out, 2 non-isolated bi-directional ports **GPIOs:**

Hardware Trigger (GPIO), Software Trigger, or PTP (IEEE 1588) **Synchronization:**

Back Panel **Interface Port Orientation:**

9 pin M8 connector **GPIO Connector Type:**

## Threading & Mounting

C-Mount **Mount:**

## Environmental & Durability Factors

-20 to 55 **Operating Temperature ( $^{\circ}\text{C}$ ):**

-30 to 60 **Storage Temperature ( $^{\circ}\text{C}$ ):**

## Regulatory Compliance

---

**Certificate of Conformance:**

[View](#)

---

**Country of Origin:**

Canada

**Imported By:**

Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

---

## Product Details

- IP67 Rated for Protection from Water Ingress, Dust and Dirt
- 5Gbase-T (5GigE) Ethernet Interface
- Supports Power over Ethernet (PoE), Simplifying Integration

LUCID Vision Labs Atlas IP67 5GigE Cameras are water ingress protected, industrial cameras designed for imaging applications requiring high bandwidth and performance in rugged environments. These cameras support the 5Gbase-T (5GigE) Ethernet interface and are Power over Ethernet (PoE), capable of 600 MB/s data transfer rates which allow for high resolution and frame rates. LUCID Vision Labs Atlas IP67 5GigE Cameras feature a C-mount and Active Sensor alignment for superior optical performance. These cameras offer a perfect balance of fast frame rates, compact size, industrial ruggedization, and an excellent price-performance ratio.

---

;