

## M16 x 1.0 Male to M6 x 1.0 Male



Stock #56-323 **20+ In Stock**

- 1 + MRP ₹2,069

**i** Price inclusive of all taxes

**ADD TO CART**

### Volume Pricing

Qty 1-9	₹2,069 each
Qty 10-24	₹1,862 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

Metric **Type:**

### Physical & Mechanical Properties

26.00 **Diameter (mm):**

1.024 **Diameter (inches):**

**Length excluding Threads (inches):**

0.276

Length excluding Threads (mm):

7.00

Total Length (inches):

0.67

Total Length (mm):

17

## Threading & Mounting

Mounting Threads:

Male: M16-1.0 x 5 L  
Male: M6-1.0 x 5 L

## Regulatory Compliance

RoHS 2015:

Exempt

Certificate of Conformance:

View

Reach 247:

Contains SVHC(s)

Country of Origin:

Japan

Imported By:

Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Product Details

- Male to Female Thread Design
- Ideal for Mating Optical Mounts and Components
- For use with 1/4-20 or M6 Breadboard Applications

Thread-To-Thread Adapters are key components when building a Benchtop Optical System. Optomechanic components feature a wide range of threads, so these adapters are an important addition to any optical lab space. M6 to 1/4"-20 adapters are used to change between English and metric configurations whereas 8-32 to 1/4"-20 adapters and Thread-To-Thread Adapters for M16 x 1.0 threaded components are ideal for a variety of mounting systems including our [Leadscrew Drive Stages](#) and [Metric Rotary Stages](#). For male to male thread adapters designed for out [TECHSPEC® Optical Mounting Posts](#), please use [TECHSPEC® Thread Adapters](#).

Thread-to-thread adapters offer versatile connection solutions for seamlessly integrating English, Metric, or mixed-thread components within optical assemblies. These adapters are constructed for durability and accommodate a range of mounting requirements, from lightweight setups to more robust mechanical stages. Whether adapting between 8-32, 1/4"-20, M6, or M16 threads, they simplify system modifications and ensure stability for demanding benchtop configurations. They are ideal for both prototyping and permanent installations where adaptability and mechanical integrity are critical.

## FAQ(s)

### What materials are used in the Thread-to-Thread Adapters?

The adapters are made from precision-machined metals to ensure durability, stability, and long-term mechanical performance in optical systems.

### Can I adapt between Metric and English thread types?

Yes, adapters such as M6 x 1.0 to 1/4"-20 allow seamless integration between Metric and English thread standards in optical setups.

### Are these adapters compatible with high-load applications?

Yes, they are designed to maintain strong, reliable connections, suitable for both lightweight optics and heavier mechanical stage assemblies.

### How critical are these adapters for building flexible optical systems?

Thread adapters are essential for expanding system compatibility, allowing users to repurpose or upgrade optical setups without major redesigns.

## Technical Information

A - Female Thread	B - Male Thread	C	D	E	Stock No.
1/4-20 x 0.25"L	M6-1.0 x 0.25"L	0.375"	0.38"	0.63"	<a href="#">#53-927</a>
M6-1.0 x 0.25"L	1/4-20 x 0.25"L	0.375"	0.38"	0.63"	<a href="#">#53-928</a>
8-32 x 0.2"L	1/4-20 x 0.25"L	0.250"	0.33"	0.58"	<a href="#">#53-929</a>
1/4-20 x 0.25"L	8-32 x 0.2"L	0.375"	0.38"	0.58"	<a href="#">#53-930</a>
M16-1.0 x 0.25"L	M6-1.0 x 0.25"L	30mm	10mm	15mm	<a href="#">#55-453</a>
M6-1.0 x 0.2"L	M16-1.0 x 0.2"L	20mm	6mm	11mm	<a href="#">#55-036</a>
M16-1.0 x 0.2"L	1/4-20 x 0.2"L	20mm	12mm	17mm	<a href="#">#55-208</a>



