

M30.5 x 0.5 Mounted IR Cut-Off Filter



Stock #49-801 [CONTACT US](#)

1 **MRP ₹20,582**

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-9	₹20,582 each
Qty 10-25	₹18,463 each
Need More?	Request Quote

Product Downloads

- STEP:step
- Curve:pdf
- PDF Drawing:pdf
- IGES:igs
- eDrawing:eprt
- EO Spec Sheet
- [Download All](#)

General

Note: AR Coating: Both Surfaces Multilayer Broadband AR

Type: Mounted Imaging Filter

Physical & Mechanical Properties

Clear Aperture CA (mm): 28.0

Outer Diameter (mm): 32.0

Substrate Thickness (mm): 2.0

Thickness with Mount (mm): 6.4

Optical Properties

Cut-Off Wavelength (nm): 750.00

Glass/Filter Number: [SCHOTT KG3](#)

Index of Refraction (n_d): 1.52

Substrate: [Schott KG-3](#)

Surface Quality: 60-40

Wavelength Range (µm): 0.3 - 2.7

Wavelength Range (nm): 300 - 2700

Threading & Mounting

Filter Thread: M30.5 x 0.50

Regulatory Compliance

RoHS 2015: [Compliant](#)

Certificate of Conformance: [View](#)

Reach 233: [Compliant](#)

Country of Origin: Germany

Imported By: Edmund Optics India Private Limited

Product Details

- UV/IR Cut or Infrared (IR) Pass Filters
- Pass Only Visible Light or Pass Only Infrared Light
- IR-Cut are Ideal for Use As Heat-Absorbing Filters

Mounted Infrared (IR) Filters are frequently used as heat-absorbing filters, letting the visible spectral range pass while the infrared rays from 780nm and above are firmly blocked. These infrared filters are often used to protect IR-sensitive sensors or in illumination systems. Mounted Infrared (IR) Filters use IR-grade fused silica, which differs from UV-grade fused silica by its reduced amount of OH- ions, resulting in higher transmission throughout the NIR spectrum and reduction of transmission in the UV spectrum. UV/IR-Cut is a multi-coated interference filter that completely blocks unwanted UV and IR radiation. It is especially recommended for applications where digital image sensors have not been fitted with an IR protection filter (or it was removed).

Note: The transmission characteristics can be permanently changed for intense radiation from UV sources with wavelengths below 320nm (i.e., Xenon lamps).

There is little effect on off-axis angles; however, it is not recommended for extreme angles of incidence. UV/VIS-Cut filters, also known as Infrared (IR) Pass Filters, absorb most of the ultraviolet and visible region and transmit the infrared region. For infrared images that combine visible and infrared light, we recommend the R-72 Infrared (IR) Pass Filter (which passes 720nm and above). Note that lenses are typically designed for the visible spectrum, so focusing adjustment is required to obtain clear images in the infrared.

Technical Information

Frequently Purchased Together



#46-545 - Mounted M30.5 x 0.5
Threaded - Red Filter
₹6,508



#46-546 - Mounted M30.5 x 0.5
Threaded - Green Filter
₹6,508



#46-547 - Mounted M30.5 x 0.5
Threaded - Blue Filter
₹6,508




#46-576 - Mounted M30.5 x 0.5 -
UV Cut-Off Filter
₹11,401



Resources

Media Type

- Application Note
- Scientific Paper
- Video
- Glossary
- FAQ




APPLICATION NOTE

The Importance of
Optical Filter
Orientation...

SPIE.

SCIENTIFIC PAPER

Advantages of
using
engineered
chalcoanide...



VIDEO

Infrared Light

