

[See all 23 Products in Family](#)

## M30.5 x 0.5 Mounted IR Cut-Off Filter



Stock **#49-801** [CONTACT US](#)

- 1 + MRP ₹20,582

**i** Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-9	₹20,582 each
Qty 10-25	₹18,463 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

AR Coating: Both Surfaces Multilayer Broadband AR **Note:**

Mounted Imaging Filter **Type:**

### Physical & Mechanical Properties

28.0 **Clear Aperture CA (mm):**

**Outer Diameter (mm):**

32.0

2.0

6.4

Substrate Thickness (mm):

Thickness with Mount (mm):

### Optical Properties

750.00

Cut-Off Wavelength (nm):

**SCHOTT KG3**

Glass/Filter Number:

1.52

Index of Refraction (n<sub>d</sub>):

**Schott KG-3**

Substrate:

60-40

Surface Quality:

0.3 - 2.7

Wavelength Range (µm):

300 - 2700

Wavelength Range (nm):

### Threading & Mounting

M30.5 x 0.50

Filter Thread:

### Regulatory Compliance

**Compliant**

RoHS 2015:

[View](#)

Certificate of Conformance:

**Compliant**

Reach 233:

Germany

Country of Origin:

Imported By:

Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Product Details

- UV/IR Cut or Infrared (IR) Pass Filters
- Pass Only Visible Light or Pass Only Infrared Light
- IR-Cut are Ideal for Use As Heat-Absorbing Filters

Mounted Infrared (IR) Filters are frequently used as heat-absorbing filters, letting the visible spectral range pass while the infrared rays from 780nm and above are firmly blocked. These infrared filters are often used to protect IR-sensitive sensors or in illumination systems. Mounted Infrared (IR) Filters use IR-grade fused silica, which differs from UV-grade fused silica by its reduced amount of OH- ions, resulting in higher transmission throughout the NIR spectrum and reduction of transmission in the UV spectrum. UV/IR-Cut is a multi-coated interference filter that completely blocks unwanted UV and IR radiation. It is especially recommended for applications where digital image sensors have not been fitted with an IR protection filter (or it was removed).

Note: The transmission characteristics can be permanently changed for intense radiation from UV sources with wavelengths below 320nm (i.e., Xenon lamps).

There is little effect on off-axis angles; however, it is not recommended for extreme angles of incidence. UV/MS-Cut filters, also known as Infrared (IR) Pass Filters, absorb most of the ultraviolet and visible region and transmit the infrared region. For infrared images that combine visible and infrared light, we recommend the R-72 Infrared (IR) Pass Filter (which passes 720nm and above). Note that lenses are typically designed for the visible spectrum, so focusing adjustment is required to obtain clear images in the infrared.

## Technical Information

