

M40.5 x 0.5 Mounted UV/IR Cut-Off Filter



Stock **#49-812** 1 In Stock

-

1

+

MRP ₹19,567

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-9	₹19,567 each
Qty 10+	₹17,637 each
Need More?	Request Quote

Product Downloads

General

AR Coating: Both Surfaces Multi-Layer	Note:
Mounted Imaging Filter	Type:

Physical & Mechanical Properties

35.8	Clear Aperture CA (mm):
	Outer Diameter (mm):

42.0	
	Substrate Thickness (mm):
2.0	
	Thickness with Mount (mm):
6.4	
Optical Properties	
	Cut-Off Wavelength (nm):
690.00	
	Cut-On Wavelength (nm):
390.00	
	Index of Refraction (n _d):
1.52 Substrate, Varies by Layer	
	Substrate:
Float Glass	
	Surface Quality:
60-40	
Threading & Mounting	
	Filter Thread:
M40.5 x0.50	
Regulatory Compliance	
	RoHS 2015:
Compliant	
	Certificate of Conformance:
View	
	Reach 233:
Compliant	
	Country of Origin:
Germany	
	Imported By:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	

Product Details

- UV/IR Cut or Infrared (IR) Pass Filters
- Pass Only Visible Light or Pass Only Infrared Light
- IR-Cut are Ideal for Use As Heat-Absorbing Filters

Mounted Infrared (IR) Filters are frequently used as heat-absorbing filters, letting the visible spectral range pass while the infrared rays from 780nm and above are firmly blocked. These infrared filters are often used to protect IR-sensitive sensors or in illumination systems. Mounted Infrared (IR) Filters use IR-grade fused silica, which differs from UV-grade fused silica by its reduced amount of OH- ions, resulting in higher transmission throughout the NIR spectrum and reduction of transmission in the UV spectrum. UV/IR-Cut is a multi-coated interference filter that completely blocks unwanted UV and IR radiation. It is especially recommended for applications where digital image sensors have not been fitted with an IR protection filter (or it was removed).
Note: The transmission characteristics can be permanently changed for intense radiation from UV sources with wavelengths below 320nm (i.e., Xenon lamps).

There is little effect on off-axis angles; however, it is not recommended for extreme angles of incidence. UV/MS-Cut filters, also known as Infrared (IR) Pass Filters, absorb most of the ultraviolet and visible region and transmit the infrared region. For infrared images that combine visible and infrared light, we recommend the R-72 Infrared (IR) Pass Filter (which passes 720nm and above). Note that lenses are typically designed for the visible spectrum, so focusing adjustment is required to obtain clear images in the infrared.

Technical Information

