

## M43.0 x 0.75 Thread, Ring Light Filter Thread Adapter



Ring Light Filter Thread Adapter. Filter Thread varies by Stock Number. (M30.5 x 0.5 Thread Shown)

Stock **#56-094** CLEARANCE 10 TO 12 DAYS

-

1

+

 ₹3,998

ADD TO CART

Qty 1+

₹3,998

Volume Pricing

[Request Quote](#)

Product Downloads

### SPECIFICATIONS

#### General

Accessory

Type of Illumination:

#### Physical & Mechanical Properties

Construction:

Anodized Aluminum

Threading & Mounting

M43.0 x0.75Filter Thread:

Regulatory Compliance

CompliantRoHS 2015:

ViewCertificate of Conformance:

CompliantReach 235:

PRODUCT DETAILS

- Compatible with LED Ring Lights
- Common Filter Thread Sizes Available
- Allows for Easy Integration of LED Ring Lights

Ring Light Filter Thread Adapters allow our LED ring lights to connect directly to an [imaging lens](#). The adapter slides into a flange protruding from the back of the ring light. Select the ring light adapter with the threading that matches the front filter threading of the lens. All feature an anodized aluminum construction.

**Note:** Though Ring Light Filter Thread Adapters can work with a wide range of imaging lenses, the working distance and field coverage provided by the LED ring light must be considered. Vignetting may occur on very wide angle imaging lenses.

TECHNICAL INFORMATION

| Filter Thread | Imaging Lenses Available to Use with Adapters                                                                                                                                                                                                                       | Adapter Stock No.       |
|---------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------|
| M25.5 x0.5    | 8.5/12/16/25/35/50/75mm <a href="#">C Series Fixed Focal Length Lenses</a>                                                                                                                                                                                          | <a href="#">#56-523</a> |
| M30.5 x0.5    | 18mm and 25mm <a href="#">DG Series FFL</a> , <a href="#">28mm Rodagon</a> , <a href="#">MegaPixel Fixed Focal Length</a> (vignetting may occur with large format sensors), <a href="#">Compact VIS-NIR Lenses</a> (vignetting may occur with large format sensors) | <a href="#">#56-089</a> |
| M34.5 x0.5    | <a href="#">3.3X Macro Zoom Lens</a>                                                                                                                                                                                                                                | <a href="#">#56-090</a> |
| M37 x0.75     | <a href="#">MMS®</a> , 35mm <a href="#">DG Series FFL</a> , 0.50X and 1.0X <a href="#">SilverTL™ Telecentric</a>                                                                                                                                                    | <a href="#">#56-091</a> |
| M39 x0.5      | 50mm <a href="#">DG Series FFL</a>                                                                                                                                                                                                                                  | <a href="#">#56-092</a> |
| M40.5 x0.5    | <a href="#">7X Close Focus Zoom</a> (vignetting may occur with large format sensors or at lowest zoom settings), 35/50/60/80/105/135mm <a href="#">Rodagon Lenses</a> , 0.60X <a href="#">SilverTL™ Telecentric Lenses</a>                                          | <a href="#">#56-093</a> |
| M43 x0.75     | <a href="#">55mm Telecentric</a> , 0.30X/0.40X/2.0X <a href="#">SilverTL™ Telecentric</a>                                                                                                                                                                           | <a href="#">#56-094</a> |
| M46 x0.75     | <a href="#">10X Close Focus Zoom</a> (vignetting may occur with large format sensors or at lowest zoom settings), 0.25X <a href="#">SilverTL™ Telecentric</a>                                                                                                       | <a href="#">#56-095</a> |
| M49 x0.75     | 75mm <a href="#">DG Series FFL</a>                                                                                                                                                                                                                                  | <a href="#">#56-096</a> |
| M52 x0.75     | <a href="#">6X Close Focus Zoom</a> (vignetting may occur with large format sensors or at lowest zoom settings), <a href="#">TECHSPEC® LS Series Fixed Focal Length Lenses</a>                                                                                      | <a href="#">#56-097</a> |
| M58 x0.75     | 0.36X/0.5X <a href="#">GoldTL™ Telecentric</a> , 0.20X/4.0X <a href="#">SilverTL™ Telecentric</a>                                                                                                                                                                   | <a href="#">#56-098</a> |
| M62 x0.75     | 0.73X/1X <a href="#">GoldTL™ Telecentric</a> , 0.16X <a href="#">SilverTL™ Telecentric</a>                                                                                                                                                                          | <a href="#">#56-099</a> |
| M72 x0.75     | 0.18X/0.25X <a href="#">GoldTL™ Telecentric</a>                                                                                                                                                                                                                     | <a href="#">#56-100</a> |

| Compatible Ring Lights                                                          |
|---------------------------------------------------------------------------------|
| <a href="#">Advanced Illumination Standard Working Distance LED Ring Lights</a> |
| <a href="#">Advanced Illumination Extended Working Distance LED Ring Lights</a> |
| <a href="#">Advanced Illumination Brightfield/Darkfield LED Ring Lights</a>     |
| <a href="#">Advanced Illumination 5" Darkfield LED Illuminators</a>             |