

## M52 x 0.75 Mounted UV/IR Cut-Off Filter



Stock #54-750 **1 In Stock**

- 1 + MRP ₹26,030

**i** Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-9	₹26,030 each
Qty 10-25	₹23,406 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

AR Coating: Both Surfaces Multi-Layer **Note:**  
 Mounted Imaging Filter **Type:**

### Physical & Mechanical Properties

52.8 **Clear Aperture CA (mm):**  
**Outer Diameter (mm):**

54.0

Substrate Thickness (mm):

2.0

Thickness with Mount (mm):

7.0

### Optical Properties

Cut-Off Wavelength (nm):

690.00

Cut-On Wavelength (nm):

390.00

Index of Refraction (n<sub>d</sub>):

1.52 Substrate, Varies by Layer

Substrate:

Float Glass

Surface Quality:

60-40

### Threading & Mounting

Filter Thread:

M52 x 0.75

### Regulatory Compliance

RoHS 2015:

Compliant

Certificate of Conformance:

[View](#)

Reach 233:

Compliant

Country of Origin:

Germany

Imported By:

Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Product Details

- UV/IR Cut or Infrared (IR) Pass Filters
- Pass Only Visible Light or Pass Only Infrared Light
- IR-Cut are Ideal for Use As Heat-Absorbing Filters

Mounted Infrared (IR) Filters are frequently used as heat-absorbing filters, letting the visible spectral range pass while the infrared rays from 780nm and above are firmly blocked. These infrared filters are often used to protect IR-sensitive sensors or in illumination systems. Mounted Infrared (IR) Filters use IR-grade fused silica, which differs from UV-grade fused silica by its reduced amount of OH- ions, resulting in higher transmission throughout the NIR spectrum and reduction of transmission in the UV spectrum. UV/IR-Cut is a multi-coated interference filter that completely blocks unwanted UV and IR radiation. It is especially recommended for applications where digital image sensors have not been fitted with an IR protection filter (or it was removed).

Note: The transmission characteristics can be permanently changed for intense radiation from UV sources with wavelengths below 320nm (i.e., Xenon lamps).

There is little effect on off-axis angles; however, it is not recommended for extreme angles of incidence. UV/MS-Cut filters, also known as Infrared (IR) Pass Filters, absorb most of the ultraviolet and visible region and transmit the infrared region. For infrared images that combine visible and infrared light, we recommend the R-72 Infrared (IR) Pass Filter (which passes 720nm and above). Note that lenses are typically designed for the visible spectrum, so focusing adjustment is required to obtain clear images in the infrared.

## Technical Information

