

[See all 33 Products in Family](#)

Micro HM Objective



ROBUSTO™ and ROBUSTO-Lite™ Cinematography Lenses



Stock #16-114 **1 In Stock**

MRP ₹1,56,114

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹1,56,114 each
Need More?	Request Quote

Product Downloads

General

Lens Accessory **Type:**

Physical & Mechanical Properties

74.50 **Length (mm):**

Optical Properties

18 - ∞ **Working Distance (mm):**

0X- 16X **Magnification:**

0.306 - 0.035 **Numerical Aperture (NA) Range:**

Threading & Mounting

C-Mount **Mounting Threads:**

Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[Compliant](#) **Reach 224:**

[View](#) **Certificate of Conformance:**

United States **Country of Origin:**

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Exceptional Micro, Macro, and Long-Distance Performance
- Enable Long Distance Imaging with Superior Detail over Depth of Field
- Six Interchangeable Objectives to Meet Application Requirements

ROBUSTO™ Cinema Production Lenses, part of Infinity Photo-Optical Company's line of Nelsonian™ Optics, incorporate Infinity's world-renowned long working distance microscope technology to provide exceptional performance for micro, macro, and long-distance cinema production and advanced photography applications. These lenses have focus and iris adjustment and are available in two models: the ROBUSTO™ or the ROBUSTO Lite™. The ROBUSTO is designed with built in gearing for focus motorization while the ROBUSTO Lite features a smaller, more lightweight body for easy manual use with an optional gear for motorization available. Both versions of the ROBUSTO lens utilize one of six interchangeable objectives to meet application requirements. In addition to their use in cinema production and photography applications, ROBUSTO Cinematography Lenses are also ideal for industrial, forensic, and biological applications where they can transform any machine vision camera into a portable, continuously-focusable microscope.

Visit the [Infinity Photo-Optical Cinema Products](#) brand page to learn more about these products!