

# MicroBrite 150mm White Line Light



Stock #74-227 NEW **1 In Stock**

MRP ₹95,049

Price inclusive of all taxes

ADD TO CART

### Volume Pricing

Qty 1+	₹95,049 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

#### General

**Type of Illumination:**  
LED Illuminator

**Note:**  
Compatible with #18-645 external controller

**Manufacturer:**  
Advanced Illumination

**Geometry:**  
Line Light

**Illumination Mode:**  
Constant

## Physical & Mechanical Properties

Length (mm):

150.00

Dimensions (mm):

174.5 L x 152.4 W x 20.1 D

Weight (g):

762

## Optical Properties

Color:

White

Working Distance (inches):

0.5-23

## Hardware & Interface Connectivity

Connector:

Flying Leads

Operating Voltage (V):

24VDC, 1.5A

Power Supply:

Power Supply Required and Sold Separately.

USA: [#66-855](#)

Europe: [#66-855](#)

Japan: [#89-513](#)

Korea: [#33-773](#)

China: [#66-855](#)

## Threading & Mounting

Mount:

M4 Mounting Screws

## Environmental & Durability Factors

Operating Temperature (°C):

0 °C to 35 °C

## Regulatory Compliance

RoHS 2015:

[Exempt](#)

Certificate of Conformance:

[View](#)

Reach 247:

[Contains SVHC\(s\)](#)

Country of Origin:

United States

Imported By:

Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Product Details

- Ideal For Line Scan Applications
- High Power LEDs in White, Red, and Blue
- Compact Form Factor for Easy Integration

The Advanced Illumination Microbrite™ Line Lights offer a compact solution for line scan applications. These lights are designed with a high intensity illumination profile and high thermal efficiency, enabling a long lifespan even with continuous operation. These illuminators feature an M4 mounting channel for ease of integration and are available in white, blue, and red wavelengths. The Advanced Illumination Microbrite™ Line Lights are ideal for line scan applications such as high speed inspection of materials including textiles, paper, or plastics and inspection of solar panels or LCDs.

[3D-Printable Mount Files](#)



Bar or Line Light Configuration

[Download Now](#)

Designed for use with the [Articulating Arm Mounting Systems](#), these 3D-printed mounts allow easy positioning of lights in brightfield or darkfield setups. The design is based on mounting illumination to 1/4-20" breadboards or into 80/20 extrusion systems, but can be adapted based on user needs. Mounts are available for ring, bar, line, and inline spot lights.



[Application Note](#)

[Illumination Mounts for Machine Vision Applications](#)

[Read](#)



[Video](#)

[Assembly of 3D Printed Mounts for Common Illumination Geometries](#)

[Watch](#)