

[See all 40 Products in Family](#)

## Model 1125, 5mW Random Polarization, Lumentum HeNe Laser



Lumentum High Performance Helium-Neon Lasers



Stock #62-722 **CLEARANCE** 1 In Stock

- 1 + MRP ₹1,44,963

ⓘ Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1+	₹1,44,963 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads



### General

Warm-Up Time (minutes):  
10

Manufacturer:  
Lumentum

Type of Laser:  
HeNe

Laser Class - CDRH:

## Model Number:

1125

## Physical &amp; Mechanical Properties

## Pointing Stability after Warm Up (mrad/°C):

After 15 min: &lt;0.02

## Weight (lbs):

1.3

## Length of Laser Head (inches):

15.79

## Static Alignment:

Centered to Outer Cylinder:  $\pm 0.01''$ Parallel to Outer Cylinder:  $\pm 1.0$  mrad

## Pointing Stability (mrad/°C):

From Cold Start, 25°: &lt;0.1

## Diameter of Laser Head (inches):

1.74

## Optical Properties

## Polarization:

Random

## Spatial Mode:

TEM<sub>00</sub>

## Wavelength (nm):

632.80

## Beam Diameter Tolerance (%):

 $\pm 3$ 

## Beam Divergence Tolerance (%):

 $\pm 3$ 

## Maximum Drift:

Mean Power over 8 hrs:  $\pm 2.5$ 

## Beam Diameter (mm):

0.81

## Beam Divergence (mrad):

1.00

## Color:

Red

Mode Purity (TEM<sub>00</sub>):

&gt;95%

## Electrical

## Output Power (mW):

5

## RMS Noise:

30 Hz - 10 MHz 0.2%

## Longitudinal Mode Spacing, Nominal (MHz):

435

Minimum Output Power, TEM<sub>00</sub> (mW):

5.0

## Hardware &amp; Interface Connectivity

## Power Supply:

#18-965 or #18-969 (12VDC), #18-966 (24VDC),  
#11-390 (110/220VAC)

## Output Type:

Free Space

## Environmental &amp; Durability Factors

## Operating Temperature (°C):

-40 to +70

## Operating Humidity:

0 to 100%, non-condensing

## Storage Temperature (°C):

-40 to +150

## Regulatory Compliance

## RoHS 2015:

Compliant

## Certificate of Conformance:

[View](#)

## REACH 241:

Compliant

## Country of Origin:

Thailand

**Imported By:**

Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Product Details

110V or 220V power supplies sold separately. These HeNe lasers comply with 21CFR1040 and IEC 825-1:1993.

- Power Options from 0.5 - 22.5mW
- Improved Stability
- Ideal for Interferometry and Metrology Applications
- Random or Linear Polarization Options

Lumentum High Performance Helium-Neon Lasers feature a patented close-cathode design that provides improved thermal and power stability. They also utilize a patented field concentrator design that enables fast turn-on. These Lumentum HeNe lasers also feature precisely aligned cylindrical housings, with cylindrical laser heads and electrical interconnect systems used to simplify system integration. Lumentum High Performance Helium-Neon Lasers' rugged design is ideal for even the most demanding applications. They are exemplary for use within interferometry and metrology applications.

**Note:** Please exercise caution when using a user-provided power supply to not exceed the electrical specifications of the laser as this may cause damage and void the warranty. These HeNe lasers comply with 21CFR1040 and IEC 825-1:1993. Lumentum was previously known as JDSU.

## Technical Information

### Beam Expander Mounting Configurations

Click on an item below to be brought to that item's product page.

