

MT-L4 Accessory Tube Lens

See More by [Mitutoyo](#)



Stock #56-864 [CONTACT US](#)

1 [-](#) [+](#) MRP ₹5,11,884

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹5,11,884 each
Need More?	Request Quote

Product Downloads

General

MT-L4 **Model Number:**

Tube Lens **Type:**

Physical & Mechanical Properties

35.00 **Diameter (mm):**

30.60 **Length (mm):**

Optical Properties

200.00	Focal Length FL (mm):
1X	Magnification:
266 - 620	Wavelength Range (nm):
24.00	Field Number (mm):
23.00	Entrance Pupil Diameter (mm):

Threading & Mounting

M32 x 0.5 pitch	Mounting Threads:
-----------------	--------------------------

Regulatory Compliance

Exempt	RoHS 2015:
View	Certificate of Conformance:
Contains SVHC(s)	REACH 241:
Japan	Country of Origin:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	Imported By:

Product Details

- Creates an Image When Used With a Mitutoyo Objective
- Low Cost Alternative to [Mitutoyo VMU](#) and [FS-70 Microscopes](#)
- [Accessory Adapters](#) Available to Ease Integration with C-Mount Cameras

Mitutoyo Tube Lenses function as secondary lenses to form an image using any of the [Mitutoyo Infinity Corrected Objectives](#). They are economical alternatives to the [FS70 Microscope](#) or [Infinite® In-line Assembly Unit](#). Several options are available, depending upon system requirements. The MT-4 and MT-40 are designed for end-user integration and can easily be used with any C-Mount camera with our Mitutoyo C-Mount Camera Extension Tube [#56-992](#). Mitutoyo Tube Lenses MT-4 Tube Lens is recommended for use with Objectives from 1X to 20X magnification, while the MT-40 is recommended for use with Objectives with >20X magnification. The MT-1 Tube Lens permits the introduction of a beamsplitter to the imaging path, allowing for a custom in-line illumination system. The MT-2 Tube Lens is similar to the MT-1 but with an effective focal length of 400mm, providing twice the stated magnification for any of the Mitutoyo objectives. The MT-L and MT-L4 lenses are designed for the [M Plan NUV](#) and [M Plan UV](#) series of objectives, respectively. [NIR and zoom tube lenses](#) are also available through our line of Precision Zoom Lenses.

Technical Information



