

[See all 9 Products in Family](#)

NIR Wire Grid Polarizer, HC, 700nm-2500nm, 25mm x 25mm



Photo shows 26-998 and 27-000 NIR Wire Grid Polarizers

Stock **#26-995** CLEARANCE **2 In Stock**

-

1

+

₹73,031

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-5	₹73,031 each
Qty 6+	₹65,957 each
Need More?	Request Quote

Product Downloads

General

Type:

Linear Polarizer

Physical & Mechanical Properties

Clear Aperture CA (mm):

19 x 19

Dimensions (mm):

25 x 25 ±0.2

5.80 ±0.2 (with mount)	Thickness (mm):
Wire Grid	Construction:
Optical Properties	
0° ±20°	Angle of Incidence (°):
Uncoated	Coating:
1100:1@900nm 3000:1@1400nm 5500:1@1900nm 5900:1@2400nm	Extinction Ratio:
Wire Grid on Display Grade Glass	Substrate: □
80-50	Surface Quality:
>81.5@900nm >87.7 @1400nm >88.9@1900nm >88.6@2400nm	Transmission (%):
700 - 2500	Wavelength Range (nm):

Threading & Mounting	
Mounted 6061 Anodized Aluminium	Mount:

Material Properties	
31.7 x 10-7/C (0 - 300°C)	Thermal Expansion:

Regulatory Compliance	
View	Certificate of Conformance:
United States	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- Designed for 700 - 2500nm
- High Transmission and High Contrast Versions Available
- Ideal for Thermal Imaging

NIR Wire Grid Polarizers are broadband polarizers designed to provide high transmission from 700 - 2500nm. These polarizers are optimized as either a high contrast version, providing 5900:1 extinction ratio at 2400nm, or as a high transmission version providing up to 91% transmission at 1900nm. NIR Wire Grid Polarizers are manufactured on high-grade display glass, providing excellent heat resistance for NIR applications . When incident light strikes the wire grid, P-polarized light contacts a dielectric and is transmitted, while S-polarized light contacts a mirror and is reflected.

Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools