

[See all 9 Products in Family](#)

## NIR Wire Grid Polarizer, HT, 700nm-2500nm, 25mm x 25mm



Photo shows 26-998 and 27-000 NIR Wire Grid Polarizers

Stock #27-000 CLEARANCE **20+ In Stock**

MRP ₹87,774

**!** Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-5	₹87,774 each
Qty 6+	₹79,199 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

Linear Polarizer **Type:**

### Physical & Mechanical Properties

19 x 19 **Clear Aperture CA (mm):**

25 x 25 ±0.2 **Dimensions (mm):**

5.80 ±0.2 (with mount) **Thickness (mm):**

Wire Grid **Construction:**

## Optical Properties

0° ±20° **Angle of Incidence (°):**

Uncoated **Coating:**

150:1@900nm  
500:1@1400nm  
800:1@1900nm  
1000:1@2400nm **Extinction Ratio:**

Wire Grid on Display Grade Glass **Substrate:** □

80-50 **Surface Quality:**

>88.1@900nm  
>91.0@1400nm  
>91.3@1900nm  
>90.3@2400nm **Transmission (%):**

700 - 2500 **Wavelength Range (nm):**

## Threading & Mounting

Mounted 6061 Anodized Aluminium **Mount:**

## Material Properties

31.7 x 10<sup>-7</sup>/°C (0 - 300°C) **Thermal Expansion:**

## Regulatory Compliance

[View](#) **Certificate of Conformance:**

United States **Country of Origin:**

Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91-80-6845 0000 **Imported By:**

## Product Details

- Designed for 700 - 2500nm
- High Transmission and High Contrast Versions Available
- Ideal for Thermal Imaging

NIR Wire Grid Polarizers are broadband polarizers designed to provide high transmission from 700 - 2500nm. These polarizers are optimized as either a high contrast version, providing 5900:1 extinction ratio at 2400nm, or as a high transmission version providing up to 91% transmission at 1900nm. NIR Wire Grid Polarizers are manufactured on high-grade display glass, providing excellent heat resistance for NIR applications. When incident light strikes the wire grid, P-polarized light contacts a dielectric and is transmitted, while S-polarized light contacts a mirror and is reflected.

## Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools