

[See all 6 Products in Family](#)

Norland Electronic Adhesive NEA 123, 10cc Dispensing Barrel

See More by [Norland](#)



Norland Electronic Adhesive NEA 121, 10cc Dispensing Barrel

Stock #21-293 **10 In Stock**

⊖ 1 ⊕ MRP ₹3,876

● Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-4	₹3,876 each
Qty 5-11	₹3,494 each
Need More?	Request Quote

Product Downloads

General

0.34 **Size (oz):**

NEA 123 **Norland Number:**

4 months **Shelf Life:**

Barrel **Type:**

Typical Applications:
High viscosity thixotropic paste for wire tacking, chip bonding, and coil terminating

Note:
Contains 10g of adhesive

Optical Properties

Absorption Range (nm):
320 - 380

Material Properties

Glass Bonding:
Excellent

Metal Bonding:
Excellent

Plastic Bonding:
Good/Excellent

Viscosity (cps):
200,000

Environmental & Durability Factors

Operating Temperature (°C):
-150 to +150 (after cured)

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 253:
[Compliant](#)

Country of Origin:
United States

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Single Component UV Curing Adhesives
- Excellent Adhesion to Glass, Metals, and Plastic
- Ideal for Potting, Sealing, and Fastening

Norland Electronic Adhesives are single component UV curing adhesives that form electrically insulating bonds when cured. These adhesives are designed for fast, precision bonding in electronic assembly applications and have excellent adhesion to glass, metals, and plastics. Each adhesive also contains a heat catalyst that can quickly cure areas that cannot be exposed to UV light. Norland Electronic Adhesives are ideal for use with circuit boards, opto-electronic devices, or other electronics for potting, sealing, wire tacking, or fastening.

Note: NEA 121 and 123 may cause skin irritation and prolonged contact with skin should be avoided; [fingercots or gloves](#) are recommended when applying these adhesives. The curing process is highly exothermic – bulk material should never be exposed to high heat or ultraviolet light.

Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools