

[See all 48 Products in Family](#)

## Norland Optical Adhesive NOA 1375, 1 oz. Application Bottle

See More by [Norland](#)



Norland Optical Adhesive NOA 1375, 1 oz. Application Bottle

Stock **#17-353** **1 In Stock**

⊖ 1 ⊕ MRP ₹12,744

① Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-4	₹12,744 each
Qty 5-11	₹11,470 each
Qty 12+	₹10,896 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

1 **Size (oz):**

1375 **Norland Number:**

4 months **Shelf Life:**

Bottle	Type:
Bonding glass to glass	Typical Applications:
UV	Cure:
<b>Optical Properties</b>	
1.375 @ 589nm	Index of Refraction ( $n_d$ ):
315 - 395	Absorption Range (nm):
<b>Material Properties</b>	
Excellent	Glass Bonding:
Good	Metal Bonding:
Fair	Plastic Bonding:
20 - 40	Viscosity (cps):
Glass to Glass	Bonding Type:
6	Energy for Full Cure ( $J/cm^2$ ):
<b>Environmental &amp; Durability Factors</b>	
Soft	Durability:
<b>Regulatory Compliance</b>	
<a href="#">Compliant</a>	RoHS 2015:
<a href="#">View</a>	Certificate of Conformance:
<a href="#">Compliant</a>	Reach 251:
United States	Country of Origin:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	Imported By:

## Product Details

- Excellent Optical Qualities
- Adhesives for Glass, Metal, and Plastic Bonding
- Cure Quickly when Exposed to UV Light
- [Preloaded Norland Optical Adhesive Syringes](#) Also Available

Norland Optical Adhesives are clear, solvent-free optical adhesives designed to fully cure in only minutes when exposed to ultraviolet light. These adhesives are used in precision alignment or positioning applications that require a robust and resilient bond. Norland Optical Adhesives feature a variety of bonding types, including but not limited to glass to glass, glass to glass/metal, and plastic to plastic/glass. To use Norland Optical Adhesives, apply the adhesive to the optical surface, position the components, and use a [UV light source](#) to set the components in place. Since the adhesive will not cure until exposed to UV light, time can be taken during the positioning process to perfect product alignment.

## Technical Information

**NORLAND OPTICAL ADHESIVES (NOA) APPLICATION NOTES**

Title	Description
<a href="#">Applying Adhesive</a>	Covers best practices to use when applying Norland Optical Adhesives to ensure an even adhesive layer while avoiding air bubbles.
<a href="#">Chemical Resistance of NOA</a>	Covers the effects of various chemicals on Norland Optical Adhesives including acids, bases, and solvents.
<a href="#">Preventing Lens Separations with NOA</a>	Covers best practices to avoid adhesive failures when bonding optical elements.
<a href="#">Separating Lenses Bonded with NOA</a>	Covers how to unbond optical elements bonded with Norland Optical Adhesives.