

[See all 48 Products in Family](#)

## Norland Optical Adhesive NOA 144, 1 oz. Application Bottle

See More by [Norland](#)



Norland Optical Adhesive NOA 144, 1 oz. Application Bottle

Stock **#17-358** **2 In Stock**

⊖ 1 ⊕ ₹10,620

**ADD TO CART**

Volume Pricing	
Qty 1-4	₹10,620 each
Qty 5+	₹10,098 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

#### General

1 **Size (oz):**

144 **Norland Number:**

4 months **Shelf Life:**

Bottle **Type:**

Bonding glass to glass **Typical Applications:**

## Optical Properties

1.44 @ 589nm **Index of Refraction (n<sub>d</sub>):**  
315 - 395 **Absorption Range (nm):**

## Material Properties

Excellent **Glass Bonding:**  
Good **Metal Bonding:**  
Fair **Plastic Bonding:**  
45 - 60 **Viscosity (cps):**  
Glass to Glass **Bonding Type:**  
6 **Energy for Full Cure (J/cm<sup>2</sup>):**

## Environmental & Durability Factors

Soft **Durability:**

## Regulatory Compliance

**Compliant** **RoHS 2015:**  
**View** **Certificate of Conformance:**  
**Compliant** **Reach 251:**  
United States **Country of Origin:**  
Edmund Optics India Private Limited **Imported By:**

## Product Details

- Excellent Optical Qualities
- Adhesives for Glass, Metal, and Plastic Bonding
- Cure Quickly when Exposed to UV Light
- [Preloaded Norland Optical Adhesive Syringes](#) Also Available

Norland Optical Adhesives are clear, solvent-free optical adhesives designed to fully cure in only minutes when exposed to ultraviolet light. These adhesives are used in precision alignment or positioning applications that require a robust and resilient bond. Norland Optical Adhesives feature a variety of bonding types, including but not limited to glass to glass, glass to glass/metal, and plastic to plastic/glass. To use Norland Optical Adhesives, apply the adhesive to the optical surface, position the components, and use a [UV light source](#) to set the components in place. Since the adhesive will not cure until exposed to UV light, time can be taken during the positioning process to perfect product alignment.

## Technical Information

NORLAND OPTICAL ADHESIVES (NOA) APPLICATION NOTES	
Title	Description
<a href="#">Applying Adhesive</a>	Covers best practices to use when applying Norland Optical Adhesives to ensure an even adhesive layer while avoiding air bubbles.
<a href="#">Chemical Resistance of NOA</a>	Covers the effects of various chemicals on Norland Optical Adhesives including acids, bases, and solvents.
<a href="#">Preventing Lens Separations with NOA</a>	Covers best practices to avoid adhesive failures when bonding optical elements.
<a href="#">Separating Lenses Bonded with NOA</a>	Covers how to unbond optical elements bonded with Norland Optical Adhesives.

