

[See all 48 Products in Family](#)

Norland Optical Adhesive NOA 76, 100g Bottle

See More by [Norland](#)



Norland Optical Adhesive NOA 76, 100g Bottle

Stock **#17-347** **5 In Stock**

MRP ₹13,063

1 Price inclusive of all taxes

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1-4 | ₹13,063 each |
| Qty 5-11 | ₹11,756 each |
| Qty 12+ | ₹11,172 each |
| Need More? | Request Quote |

Product Downloads

General

3.52 **Size (oz):**

76 **Norland Number:**

4 months **Shelf Life:**

| | |
|--|---|
| Bottle | Type: |
| Typical Applications: Bonding acrylic, polycarbonate, and other plastics to glass | |
| UV/MS | Cure: |
| Optical Properties | |
| 1.51 @ 589nm | Index of Refraction (n_d): |
| 315 - 450 | Absorption Range (nm): |
| Material Properties | |
| Excellent | Glass Bonding: |
| Good | Metal Bonding: |
| Excellent | Plastic Bonding: |
| 3500 - 5500 | Viscosity (cps): |
| Glass to Plastic | Bonding Type: |
| 5 | Energy for Full Cure (J/cm²): |
| Environmental & Durability Factors | |
| Soft & Resilient | Durability: |
| Regulatory Compliance | |
| Compliant | RoHS 2015: |
| View | Certificate of Conformance: |
| Compliant | Reach 251: |
| United States | Country of Origin: |
| Imported By: Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000 | |

Product Details

- Excellent Optical Qualities
- Adhesives for Glass, Metal, and Plastic Bonding
- Cure Quickly when Exposed to UV Light
- [Preloaded Norland Optical Adhesive Syringes](#) Also Available

Norland Optical Adhesives are clear, solvent-free optical adhesives designed to fully cure in only minutes when exposed to ultraviolet light. These adhesives are used in precision alignment or positioning applications that require a robust and resilient bond. Norland Optical Adhesives feature a variety of bonding types, including but not limited to glass to glass, glass to glass/metal, and plastic to plastic/glass. To use Norland Optical Adhesives, apply the adhesive to the optical surface, position the components, and use a [UV light source](#) to set the components in place. Since the adhesive will not cure until exposed to UV light, time can be taken during the positioning process to perfect product alignment.

Technical Information

NORLAND OPTICAL ADHESIVES (NOA) APPLICATION NOTES

| Title | Description |
|--|---|
| Applying Adhesive | Covers best practices to use when applying Norland Optical Adhesives to ensure an even adhesive layer while avoiding air bubbles. |
| Chemical Resistance of NOA | Covers the effects of various chemicals on Norland Optical Adhesives including acids, bases, and solvents. |
| Preventing Lens Separations with NOA | Covers best practices to avoid adhesive failures when bonding optical elements. |
| Separating Lenses Bonded with NOA | Covers how to unbond optical elements bonded with Norland Optical Adhesives. |