

Ocean Optics SR6 VIS-NIR Versatile Spectrometer

See More by [Ocean Optics](#)



Stock **#90-023** NEW **1 In Stock**

-

1

+

₹4,47,615

ADD TO CART

Volume Pricing	
Qty 1+	₹4,47,615 each
Need More?	Request Quote

Product Downloads

General	
OceanDirect & OceanView	
Software:	
7.2 ms – 5 s	
Integration Time:	
SR-6VN500-25	
Model Number:	
Includes manual QR code, software QR code, calibration reports for wavelength and linearity, 1 m USB cable	
Note:	

SMA905	Input Port Termination:
Ruled Diffraction Grating: 600 Grooves/mm, Blazed @ 500nm	Grating:

Cross Czerny Turner	Optical Bench:
---------------------	----------------

Physical & Mechanical Properties

25	Slit Width (µm):
0.275	Weight (kg):

88.1 x63.5 x31.45	Dimensions (mm):
-------------------	------------------

Optical Properties

1.65	Spectral Resolution (nm):
350 - 1040	Wavelength Range (nm):

Sensor

CCD	Type of Sensor:
-----	-----------------

Electrical

Single Scan @ 10 ms: 400:1 Max per second with High Speed Averaging Mode: 3500:1	Signal to Noise S/N Ratio:
---	----------------------------

Hardware & Interface Connectivity

USB, RS-232	Computer Interface:
-------------	---------------------

Threading & Mounting

(3) 4-40	Mounting Threads:
----------	-------------------

Environmental & Durability Factors

0 to +55	Operating Temperature (°C):
-30 to +70	Storage Temperature (°C):

0.03 Pixel/°C	Thermal Stability:
---------------	--------------------

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:

Compliant	Reach 250:
-----------	------------

United States	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- Compact Design and Powerful Performance
- Broad Wavelength Range Options Spanning 180 - 1040nm
- Three Models Available for a Diverse Range of Applications

Ocean Optics SR Versatile Spectrometers are available in S2, S4, and S6 models, each of which offers high performance and broad spectral coverage to suit a diverse set of applications. SR2 spectrometers are optimized for fast spectral acquisition and high signal-to-noise ratio (SNR), making them ideal for applications such as laser characterization, plasma monitoring, and absorbance concentration. The SR4 spectrometers present superior thermal wavelength stability, low-noise CCD detection, and consistent high signal-to-noise performance, perfect for plasma monitoring and reflection measurements. High-sensitivity SR6 models provide exceptional SNR and UV response, supporting applications such as UV absorbance, fluorescence, and plasma diagnostics. The Ocean Optics SR Versatile Spectrometers include the user-friendly OceanView software system to optimize spectrometer performance, ease system integration, and access data for analysis.