

[See all 13 Products in Family](#)

Optical Chopper Replacement Disc Pack (5 Discs: 2, 5, 10, 30, 200 Slots)



High Frequency Optical Chopper



Stock **#56-071** **1 In Stock**

MRP ₹54,162

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹54,162 each
Need More?	Request Quote

Product Downloads

Physical & Mechanical Properties

Construction:
Half Hard Brass, Chemically Blackened Finish

Diameter (mm):
102.00

Thickness (mm):
0.50

Regulatory Compliance

Certificate of Conformance:

[View](#)

United Kingdom

Country of Origin:

Imported By:

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91-80-6845 0000

Product Details

- Range of Interchangeable Chopping Discs
- Frequencies Ranging from 5Hz to 110 kHz
- Manual or External Frequency Control

Optical Choppers are used to mechanically modulate light sources that pass through their discs. These optical choppers include a range of interchangeable discs from 2 to 200 slots for the standard chopper and 445 slots for the high frequency chopper, supporting frequencies up to 20kHz and up to 110kHz respectively. Chopping frequency can be adjusted by either a ten-turn dial or by applying an external DC voltage to the "Control In" BNC port on the front panel. Optical Choppers are ideal for use in a variety of applications including Lock-in Detection, Fluorescence Decay Measurement, Rotation Detection, and Reduction of Average Power. These choppers feature a "Reference Out" BNC port that provides a TTL pulse at the chopping frequency and in phase with the chopping action.

Please exercise caution when utilizing the high frequency chopper, [#28-115](#), in applications where it is not possible to completely remove the danger of finger ingress. For safe operation a blanking plate is included to cover all unused apertures and to reduce the size of the aperture in use. High chopping frequencies also lead to heated jets of air to be released through any open apertures in the blade protector and operation is loud and should be considered for applications where noise is a concern. Please ensure the chopper head is securely bolted to the operating surface due to vibrations from the high chopping frequencies.

Technical Information

