


TECHSPEC[®] Optotune Industrial 4 Channel Current Controller | ICC-4C-500



Optotune Industrial 4 Channel Controller | ICC-4C-500 (#22-408)



Stock **#22-408** 1 In Stock

-

1

+

₹1,25,280

ADD TO CART

Volume Pricing	
Qty 1+	₹1,25,280 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Lens Accessory

Type:

Physical & Mechanical Properties

44	Height (mm):
164.00	Length (mm):
105.00	Width (mm):
Electrical	
-500 to +500	Operating Current (mA):
25 (maximum)	Power Consumption (W):
Hardware & Interface Connectivity	
Micro USB, Ethernet (to PC), 6-way Hirose (to lens)	Connector:
Environmental & Durability Factors	
0 to +60	Operating Temperature (°C):
-40 to +85	Storage Temperature (°C):
Regulatory Compliance	
View	Certificate of Conformance:

PRODUCT DETAILS

- Liquid Lens for Extended Depth of Field Telecentric Lens
- Up to 2.3 MegaPixels, 4.5µm Pixel Size Sensors
- Up to 2/3", C-Mount Telecentric Lens
- Magnification from 0.15X to 0.75X

TECHSPEC® MercuryTL™ Liquid Lens Telecentric Lenses combine the capabilities of a telecentric lens with the flexibility of a liquid lens. These lenses combine the unique feature of telecentric lenses, eliminating parallax (or perspective) error, with a liquid lens, allowing for the focus to be electronically controlled. This combination provides quick working distance adjustment, while maintaining telecentricity, distortion, and image performance throughout the entire working distance range. TECHSPEC® MercuryTL™ Liquid Lens Telecentric Lenses are ideal for gauging, measurement, and placement applications where quick depth of field adjustment is required.

As the liquid lens is used to focus the telecentric lens, its curvature changes. As its curvature changes, there will be small changes in the ray angles in the rear of the lens (incident on the image sensor). As a result, there are small field of view changes over the working distance range as the liquid lens refocuses the lens. However, the front (object space) ray angles are unaffected by the liquid lens changing curvature, allowing the telecentric lens to maintain telecentricity over the entire working distance range.

Note: Hirose cables and [Liquid Lens Driver](#) sold separately.

TECHNICAL INFORMATION

