

[See all 65 Products in Family](#)

Pedestal Post, Metric, 101.6mm



Pedestal Post

Stock **#15-844** **5 In Stock**

MRP ₹4,237

! Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-4	₹4,237 each
Qty 5-9	₹3,834 each
Qty 10+	₹3,763 each
Need More?	Request Quote

Product Downloads

General

Metric **Type:**

With M6x1.0 screw holes on the base **Note:**

Pedestal Post **Function:**

Physical & Mechanical Properties

101.60 **Length (mm):**

Stainless Steel **Construction:**

0.41 **Weight (kg):**

25.4 **Post Diameter (mm):**

31.5 **Base Diameter (mm):**

Threading & Mounting

M4x0.7 **Mounting Threads:**

Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **Reach 247:**

Taiwan **Country of Origin:**

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000




Product Details









- 1" Diameter Posts with Metric and English Mounting Hole Options
- Stainless Steel Construction for High Stability
- 0.5" - 4.0" Heights Available
- Refer to the Technical Information Tab to Find the Right Adapter for your Optical Mount and Application

Pedestal Posts and Accessories offer a stable way to mount optical components to a lab table with a consistent mounting height, providing predictable and repeatable mounting of components within an optical system. A variety of pedestal extenders and shim plates are available to ensure that the optical axis height is consistent for all mounted components. Pedestal Posts feature M4 x 0.7 or 8-32 tapped holes on the top surface, compatible with [TECHSPEC® Kinematic Mounts](#), [E-Series Kinematic Mounts](#), [Compact Mirror Mounts](#), and many other [optical mounts](#). M6 x 1.0 or ¼"-20 tapped holes on the bottom surface make these Pedestal Posts directly mountable to Edmund Optics [stages](#) and [breadboards](#). For more compact table mounting, use the [Compact Mounting Clamps \(#16-335\)](#).

Note: Optical Mount Adapters are available to ensure consistent optical axis height and mounting hole compatibility with Edmund Optics' Optical Mounts. Refer to the Technical Information tab to find the right adapter for your application.

Technical Information

PEDESTAL POSTS AND ACCESSORIES					
Compatible Optic Mount	Optical Size	Mount Stock Number	Extension Length (mm)	Extender Stock Number for English Pedestals	Extender Stock Number for Metric Pedestals
 <p>Optic Component Mount</p>	50mm Dia.	#64-567	16.8	#16-321	#16-315
	2"/50.8mm Dia.	#64-569	16.8	#16-324	#16-587
 <p>Bar-Type Lens / Filter Holder</p>	1"/25.4mm Dia	#03-676	18	#16-325	#16-588
	2 axis: 2"/50.8mm Dia.	#62-957	8	#16-317	#16-311
	3 axis: 1"/25.4mm Dia.	#62-959	18	#16-222	#16-316
	5 axis: 1"/25.4mm Dia.	#13-776	18	#16-222	#16-316
	2"/50.8mm Dia.	#03-669	11	#16-323	#16-586
	2"/50.8mm Dia.	#55-530	16	#16-320	#16-314
 <p>Multi-Axis Adjustable Optic</p>	2 axis: 1"/25.4mm Dia.	#62-956	20.8	#16-460	#16-459

Multi-Axis Adjustable Optic Mounts					
 <p>Retangular Bar Clamp</p>	2"/50.8mm Sq.	#54-995	11	#16-318	#16-312
 <p>Filter Mount</p>	2"/50.8mm Sq.	#54-997	14	#16-319	#16-313
 <p>Multiple Filter Holder</p>	30mm Dia.	#55-006	16	#16-320	#16-314
 <p>Spring Mount Filter Holder</p>	2"/50.8mm Sq.	#55-531	16	#16-320	#16-314
 <p>Prism Mounts</p>	25mm Cube	#55-013	18	#16-322	#16-316
	50mm Cube	#53-027	18	#16-325	#16-588
 <p>Polarizer</p>	1"/25.4mm Dia.	#55-011	18	#16-322	#16-316
	2"/50.8mm Dia.	#56-329	8	#16-317	#16-311
 <p>Top Adjustment Kinematic Mount</p>	1"/25.4mm Dia.	#55-456	14	#16-319	#16-313
 <p>Gimbal Mount</p>	2"/50.8mm Dia.	#55-000	11	#16-318	#16-312