

[See all 10 Products in Family](#)

Coherent® Thermopile Power Sensor 1098412 | 150W, DB25

See More by [Coherent®](#)



Stock **#88-415** 20+ In Stock

-

1

+

₹1,39,500

ADD TO CART

Volume Pricing	
Qty 1+	₹1,39,500 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Model Number:

PM150-50C
Coherent Part Number: 1098412

Type:

[Meter required](#)

±1	Calibration Uncertainty (%):
1 - 150	Long Pulse Joule Mode Range (J):
Water/Air	Cooling Method:
0.6 @ 1064nm, 10ns	Maximum Incident Energy Density (J/cm²):
Compatible Meters: #35-203 , #12-393 , #59-978 , #88-411 , #66-277 , #88-412	

Physical & Mechanical Properties

50	Active Area Diameter (mm):
----	----------------------------

Optical Properties

514	Calibration Wavelength (nm):
250 - 11000	Wavelength Range (nm):
0.25 - 11	Wavelength Range (µm):

Sensor

Thermopile	Type of Sensor:
------------	-----------------

Electrical

80 (air-cooled)	Maximum Intermittent Power, <5min (W):
6	Maximum Incident Power Density (kW/cm²):
300mW - 150W	Power Range:

Hardware & Interface Connectivity

2.0	Length of Cable (m):
DB25	Computer Interface:

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:

PRODUCT DETAILS

- Superior Damage Resistance
- Wide Dynamic Range
- ISO 17025 Certified

Coherent® Thermopile Power Sensors are ideal for measuring the average power of continuous wave lasers or pulsed laser energy. Thermopile sensors operate by absorbing and converting incident laser radiation into heat, which then flows to a heat sink. The temperature difference between the absorber and heat sink is converted into an electrical signal by a thermocouple junction. Coherent® Thermopile Power Sensors, unlike semiconductor sensors, do not saturate. Unlike semiconductor sensors, thermopile sensors feature high power capability and flat spectral response.