

TECHSPEC[®] Polarization Tester



Polarization Tester

Stock #37-699 20+ In Stock

-

1

+

₹2,880

ADD TO CART

Volume Pricing	
Qty 1+	₹2,880 each
Need More?	Request Quote

Product Downloads

General	
Polarization Tester	Type:
Physical & Mechanical Properties	
200.00	Length (mm):
0.75	Thickness (mm):
Polarizing Film	Construction:

20.00	Width (mm):
Optical Properties	
42	Transmission (%):
400 - 700	Wavelength Range (nm):
Regulatory Compliance	
Compliant	RoHS 2015:
Compliant	Reach 224:
View	Certificate of Conformance:
Germany	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- Determines the Polarization Direction of Linear and Circular Polarizers
- Convenient Lightweight and Handheld Design
- Ideal for Verifying Polarizer Alignment
- Excellent for Determining the Polarization Direction of LCDs

The TECHSPEC® Polarization Tester is designed to determine different characteristics of unknown polarizers, such as the polarization direction of linear polarizers and the rotational direction of circular polarizers. This easy-to-use, handheld, compact tool is compatible with all mounted and unmounted polarizers and features regions designed to test linearly polarized light, along with right- and left-handed circularly polarized light. For circular polarizers, the tester allows for identifying the rotational direction of polarization and the position of the retarder and linear polarizer. The TECHSPEC® Polarization Tester is an ideal way of identifying the correct polarizer or verifying accurate alignment in an application. For best results, ensure that all protective films are removed from the polarizer before testing.

Note: To mount the polarization tester, [#54-997](#) is recommended.