

[See all 40 Products in Family](#)

Power Supply for 0.5-0.8mW HeNe Laser, AC, Bare Wire Leads



AC with Bare Leads HeNe Power Supply (#11-379, #11-380)

Stock **#11-379** [CONTACT US](#)

-

1

+

₹48,852

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹48,852 each
Need More?	Request Quote

Product Downloads



General

Type:

OEM

Compatible Laser Models:

[1108](#), [1108P](#), [1107](#), [1107P](#)

Model Number:

L92 Series

Compatible Laser Stock Number:

[#62-714](#), [#62-715](#), [#62-716](#), [#62-717](#)

Features:

CDRH Delay (3-5 seconds)

Physical & Mechanical Properties

4.25 x 3.30 x 1.20
Dimensions (inches):

Electrical

5
Output Power (W):
0.55/0.32
Input Current (A):

Hardware & Interface Connectivity

1250
Output Voltage (V):
4
Output Current (mA):
High Voltage Alden Connector
Connector:
100/110/220 (AC)
Input Voltage (V):

Regulatory Compliance

View
Certificate of Conformance:
United States
Country of Origin:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000
Imported By:

Product Details

- Power Options from 0.5 - 22.5mW
- Improved Stability
- Ideal for Interferometry and Metrology Applications
- Random or Linear Polarization Options

Lumentum High Performance Helium-Neon Lasers feature a patented close-cathode design that provides improved thermal and power stability. They also utilize a patented field concentrator design that enables fast turn-on. These Lumentum HeNe lasers also feature precisely aligned cylindrical housings, with cylindrical laser heads and electrical interconnect systems used to simplify system integration. Lumentum High Performance Helium-Neon Lasers' rugged design is ideal for even the most demanding applications. They are exemplary for use within interferometry and metrology applications.

Note: Please exercise caution when using a user-provided power supply to not exceed the electrical specifications of the laser as this may cause damage and void the warranty. These HeNe lasers comply with 21CFR1040 and IEC 825-1:1993. Lumentum was previously known as JDSU.

Technical Information

Beam Expander Mounting Configurations

Click on an item below to be brought to that item's product page.

