

[See all 39 Products in Family](#)

Power Supply for 10mW HeNe Laser, AC, Bare Wire Leads



SL93 Series Power Supply (#11-381)

Stock #11-381 **20+ In Stock**

⊖ 1 ⊕ MRP ₹74,340

● Price inclusive of all taxes

ADD TO CART

Volume Pricing

Qty 1+	₹74,340 each
Need More?	Request Quote

Product Downloads



General

OEM **Type:**

[1135, 1135P](#) **Compatible Laser Models:**

SL93 Series **Model Number:**

[#62-726, #62-727](#) **Compatible Laser Stock Number:**

Features:

Physical & Mechanical Properties

7.05 x 2.30 x 1.40 **Dimensions (inches):**

Electrical

20.15 **Output Power (W):**

0.75 (Max. Current Draw) **Input Current (A):**

Hardware & Interface Connectivity

3100 **Output Voltage (V):**

6.5 **Output Current (mA):**

High Voltage Alden Connector **Connector:**

100-250, 60/50Hz **Input Voltage (V):**

Regulatory Compliance

[View](#) **Certificate of Conformance:**

United States **Country of Origin:**

Imported By:
 Edmund Optics India Private Limited
 267, Greystone Building, Second Floor,
 6th Cross Rd, Binnamangala,
 Stage 1, Indiranagar, Bengaluru,
 Karnataka, India 560038
 Phone: +91- 80-6845 0000

Product Details

- Power Options from 0.5 - 22.5mW
- Improved Stability
- Ideal for Interferometry and Metrology Applications
- Random or Linear Polarization Options

Lumentum High Performance Helium-Neon Lasers feature a patented close-cathode design that provides improved thermal and power stability. They also utilize a patented field concentrator design that enables fast turn-on. These Lumentum HeNe lasers also feature precisely aligned cylindrical housings, with cylindrical laser heads and electrical interconnect systems used to simplify system integration. Lumentum High Performance Helium-Neon Lasers' rugged design is ideal for even the most demanding applications. They are exemplary for use within interferometry and metrology applications.

Note: Please exercise caution when using a user-provided power supply to not exceed the electrical specifications of the laser as this may cause damage and void the warranty. These HeNe lasers comply with 21CFR1040 and IEC 825-1:1993. Lumentum was previously known as JDSU.

Technical Information

Beam Expander Mounting Configurations

Click on an item below to be brought to that item's product page.

