

[See all 39 Products in Family](#)

Power Supply for 5-7mW HeNe Laser, 12 VDC, Advanced



SL23120 Series HeNe Laser Power Supply

Stock #18-969 [CONTACT US](#)

⊖ 1 ⊕ MRP ₹48,109

● Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹48,109 each
Need More?	Request Quote

Product Downloads



General

OEM **Type:**

Compatible Laser Models:
1125, 1125P, 1137, 1137P

Note:
Advanced power supplies include an active filter to reduce current ripple and noise. Additional heat sinking is not required.

L23 Series **Model Number:**

Compatible Laser Stock Number:
#62-722, #62-723, #62-724, #62-725

Physical & Mechanical Properties

4.25 x 3.30 x 1.20 **Dimensions (inches):**

Electrical

2.5-25 **Output Power (W):**

5.1 (Max. Current Draw) **Input Current (A):**

Hardware & Interface Connectivity

2300 **Output Voltage (V):**

6 **Output Current (mA):**

High Voltage Aiden Connector **Connector:**

10-14 DC **Input Voltage (V):**

Regulatory Compliance

[View](#) **Certificate of Conformance:**

United States **Country of Origin:**

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Power Options from 0.5 - 22.5mW
- Improved Stability
- Ideal for Interferometry and Metrology Applications
- Random or Linear Polarization Options

Lumentum High Performance Helium-Neon Lasers feature a patented close-cathode design that provides improved thermal and power stability. They also utilize a patented field concentrator design that enables fast turn-on. These Lumentum HeNe lasers also feature precisely aligned cylindrical housings, with cylindrical laser heads and electrical interconnect systems used to simplify system integration. Lumentum High Performance Helium-Neon Lasers' rugged design is ideal for even the most demanding applications. They are exemplary for use within interferometry and metrology applications.

Note: Please exercise caution when using a user-provided power supply to not exceed the electrical specifications of the laser as this may cause damage and void the warranty. These HeNe lasers comply with 21CFR1040 and IEC 825-1:1993. Lumentum was previously known as JDSU.

Technical Information

Beam Expander Mounting Configurations

Click on an item below to be brought to that item's product page.

□